

Eaton FWH-020A6F

Catalog Number: FWH-020A6F

Eaton Bussmann series FWH high speed fuse, DC common bus, 20A RMS (200% minimum opening current at rated voltage), 50 kAIC at 0.25-20A, 20 kAIC at 25-30A, Ferrule end X ferrule end, Standard

General specifications

Product Name	Catalog Number
Eaton Bussmann series FWH high speed fuse	FWH-020A6F
	UPC
	051712796729
EAN	Product Length/Depth
5027590061186	1.25 in
Product Height	Product Width
0.25 in	0.25 in
Product Weight	Warranty
0.4 lb	Not Applicable
Compliances	Certifications
CE Marked	UL Recognized
	CSA Certified



Electrical rating

Amperage Rating

20A RMS (200% minimum opening current at rated voltage)

Interrupt rating

50 kAIC at 0.25-20A

20 kAIC at 25-30A

Voltage rating

500 Vac/dc (35-800 A only)

Watt losses

4.26 W

Physical details

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non Indicating

Resources

Specifications and datasheets

[Eaton Specification Sheet - FWH-020A6F](#)

Technical data sheets

[Bussmann series FWH 6x32mm high speed fuse data sheet no. 720038](#)

[FWH-020A6F~REPLACED BY FWH5-020A6F](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)