

Eaton FWH-800A

Catalog Number: FWH-800A

Eaton Bussmann series FWH high speed fuse, 700 Vac (UL), 690 Vac (IEC), 500 Vdc (2-100A), 500 Vac, 800A RMS, 200 kAIC at 1000 Vac, 50 kAIC at 500 Vdc, Non Indicating, High speed fuse, Blade end X blade end, Stud

General specifications

| Product Name | Catalog Number |
|---|-----------------------------|
| Eaton Bussmann series FWH high speed fuse | FWH-800A |
| | UPC 051712150248 |
| Product Length/Depth | Product Height |
| 8 in | 2.59 in |
| Product Width | Product Weight |
| 2.48 in | 1.96 lb |
| Warranty | Compliances |
| Not Applicable | CE Marked RoHS Compliant |
| Certifications | |
| UL Recognized CSA Certified | |



Electrical rating

Amperage Rating

800A RMS

Interrupt rating

50 kAIC at 500 Vdc

200 kAIC at 1000 Vac

Voltage rating

700 Vac (UL), 690 Vac (IEC), 500 Vdc (2-100 A), 500 Vac

Watt losses

129 W

Physical details

Packaging type

Standard

General information

Connection

Blade end x blade end

Fuse indicator

Non Indicating

Mounting method

Stud

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Specifications and datasheets

Eaton Specification Sheet - FWH-800A

Technical data sheets

Bussmann series FWH 6x32mm high speed fuse data sheet no. 720038

[FWH-800A-BUSS HIGH SPEED FUSE](#)

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)