

Eaton BK/GMA-250-R

Catalog Number: BK/GMA-250-R

Eaton GMA Series Fast-acting fuse 0.250A, 250 Vac, 32 Vdc (self certified), BK-GMA-250-R

General specifications

| | |
|--|----------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series GMA fast-acting fuse | BK/GMA-250-R |
| | UPC |
| | 051712647274 |
| EAN | Product Length/Depth |
| 5027590254618 | 20 mm |
| Product Height | Product Width |
| 5 mm | 5 mm |
| Product Weight | Warranty |
| 0.002 kg | Not Applicable |
| Compliances | |
| CE Marked | |
| RoHS Compliant | |

Product specifications

Fuse indicator

Non-indicating

Interrupt rating

35 AIC at 250 Vac

10 kAIC at 125 Vac

Type

Electronic

Used with

out axial leads

Connection

Ferrule end x ferrule end

Response time

60 min at 135%, 2 min at 200%

Quantity

100

Material

Silver-plated brass endcap construction

Glass tube

Voltage rating

250 Vac, 32 Vdc (self certified)

Application

Electronic circuits

Amperage Rating

0.250A

Resources

Specifications and datasheets

[Eaton Specification Sheet - BK/GMA-250-R](#)

[Eaton GMA time delay glass tube fuses data sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)