

Eaton JJS-100

Catalog Number: JJS-100

Eaton Bussmann series JJS fuse, Current-limiting very fast acting fuse, Small footprint, VFD line protection, 100 A, Class T, Non-indicating, Bolted blade end x bolted blade end, 200 kAIC at 600 V, Standard, 5, 600 V

General specifications

| | |
|--------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series JJS fuse | JJS-100 |
| UPC | Product Length/Depth |
| 051712628020 | 2.95 in |
| Product Height | Product Width |
| 0.75 in | 0.75 in |
| Product Weight | Warranty |
| 0.0088 lb | Not Applicable |
| Compliances | |
| CE Marked | |
| RoHS Compliant | |

Electrical rating

Amperage Rating

100 A

Interrupt rating

200 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Packaging type

Standard

General information

Class

Class T

Connection

Bolted blade end x bolted blade end

Fuse indicator

Non-indicating

Quantity

5

Special features

Small footprint

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - JJS-100](#)

Technical data sheets

[JJS-100~TRON FAST ACTING FUSE CLASS T](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)