

Eaton JJS-400

Catalog Number: JJS-400

Eaton Bussmann series JJS fuse, Current-limiting very fast acting fuse, Small footprint, VFD line protection, 400 A, Class T, Non-indicating, Bolted blade end x bolted blade end, 200 kAIC at 600 V, Standard, 1, 600 V

General specifications

Product Name	Catalog Number
Eaton Bussmann series JJS fuse	JJS-400
UPC	Product Length/Depth
051712628044	3.63 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.5 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	



Electrical rating

Amperage Rating

400 A

Interrupt rating

200 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Packaging type

Standard

General information

Class

Class T

Connection

Bolted blade end x bolted blade end

Fuse indicator

Non-indicating

Quantity

1

Special features

Non-indicating

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - JJS-400](#)

Technical data sheets

[JJS-400~TRON FAST ACTING FUSE CLASS T](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)