

# Eaton JJS-45

Catalog Number: JJS-45

Eaton Bussmann series JJS fuse, Current-limiting very fast acting fuse, Small footprint, VFD line protection, 45 A, Class T, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 V, Standard, 10, 600 V

## General specifications

Product Name	Catalog Number
Eaton Bussmann series JJS fuse	JJS-45
UPC	Product Length/Depth
051712628457	1.56 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Warranty
0.5 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

## Electrical rating

### Amperage Rating

45 A

### Interrupt rating

200 kAIC at 600 Vac

### Voltage rating

600 V

## Physical details

### Packaging type

Standard

## General information

### Class

Class T

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Quantity

10

### Special features

Non-indicating

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - JJS-45](#)

### Technical data sheets

[JJS-45~TRON FAST ACTING FUSE CLASS T](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)