

Eaton PV-20A10F

Catalog Number: PV-20A10F

Eaton Bussmann series photovoltaic fuses, 1000 Vdc, 20A, 50 kAIC, Non Indicating, IEC 60269-6 type A, Class gPV, Time constant: 1-3 ms, Ferrule end x ferrule end

General specifications

Product Name	Catalog Number
Eaton Bussmann series photovoltaic fuses	PV-20A10F
	UPC
	051712358231
EAN	Product Length/Depth
5027590505802	38 mm
Product Height	Product Width
10 mm	10 mm
Product Weight	Warranty
9.7 g	Not Applicable
Compliances	Certifications
RoHS Compliant	UL Listed
CE Marked	CSA Certified
	IEC Rated
	UL Listed Class NKCR2
	CCC Marked



Electrical rating

Amperage Rating

20 A

Voltage rating

1000 Vdc

Watt losses

2.1 W

Breaking capacity

50 kA

Class

Class gPV

Physical details

Fuse type

PV-A10F

Fuse size

10 x 38 mm

Material

Ceramic

Compatible fuse holder

Suitable for

CHPV Modular fuse holder

HPV-DV Inline holder

Resources

Catalogs

[Eaton Bussmann Series Photovoltaic Fuses Catalogue](#)

[Bussmann series complete full line catalog no. 1007](#)

Compliance information

[UKCA Cylindrical PV fuse-links](#)

[CE Cylindrical PV fuse-links](#)

Specifications and datasheets

[Eaton Specification Sheet - PV-20A10F](#)

Technical data sheets

[720110 10x38 mm PV fuses](#)