

MISCELLANEOUS

Threaded Rod		
Trade Size	Type 304 Part Number	Type 316 Part Number
½"	S40212TR00	S60212TR00
¾"	S40312TR00	S60312TR00
1"	S40512TR00	S60512TR00

• Sold in 12' Lengths



Rod Couplings	
Trade Size	Type 316 Part Number
¼"	S60200RC00
¾"	S60300RC00
½"	S60500RC00
¾"	S60700RC00



Escutcheon Plates/Wall Flanges		
Trade Size	OD	Part Number
½"	3"	S40500EP00
¾"	3"	S40700EP00
1"	3"	S41000EP00
1 ¼"	6"	S41200EP00
1 ½"	6"	S41500EP00
2"	6"	S42000EP00
2 ½"	6"	S42500EP00
3"	6"	S43000EP00
4"	6"	S44000EP00



Wedge Anchors	
Trade Size	Part Number
VARIOUS	S60000WR00



Drop-In Anchors	
Trade Size	Part Number
¼"	S60200DR00
¾"	S60300DR00
½"	S60500DR00
¾"	S60600DR00
¾"	S60700DR00



Floor Flanges	
Trade Size	Part Number
½"	S60500FF00
¾"	S60700FF00
1"	S61000FF00
1 ¼"	S61200FF00
1 ½"	S61500FF00
2"	S62000FF00



Standard U-Bolts								
Trade Size	A	B	C	D	E	F	Wt. (lbs)	Part Number
½"	¼"	0.950"	1.400"	2.750"	2.250"	2.313"	10	S60500UB00
¾"	¼"	1.250"	1.650"	2.500"	2.250"	2.219"	11	S60700UB00
1"	¼"	1.375"	1.825"	2.750"	2.500"	2.094"	12	S61000UB00
1 ¼"	¾"	1.750"	2.350"	3.000"	2.500"	2.031"	28	S61200UB00
1 ½"	¾"	2.000"	2.700"	3.000"	2.500"	2.063"	29	S61500UB00
2"	¾"	2.438"	2.813"	3.250"	2.500"	2.063"	32	S62000UB00
2 ½"	½"	3.000"	3.875"	3.750"	3.000"	2.250"	73	S62500UB00
3"	½"	3.650"	4.500"	4.000"	3.000"	2.250"	79	S63000UB00
3 ½"	½"	4.063"	4.563"	4.250"	3.000"	2.250"	82	S63500UB00
4"	½"	5.375"	5.375"	4.750"	3.000"	2.250"	50	S64000UB00

