



Representative

**Catalog Number:** 3090-N-40-SQ  
**Product ID:** 7TAA040980R0022  
**UPC Number:** 78635850309  
**Status:** Active

Round Ceiling/Fixture Nail-On Outlet Box, Volume 13.5 Inches, Diameter 3-1/2 Inches, Depth 2-1/8 Inches, Color Brown, Material Phenolic, Mounting Means N Bracket, Robertson Head Screw, with High Clamps and #40 Ground Strap

### North American Specifications (UNSPSC)

UNSPSC	39121308 Outlet box
IGCC	4433 Outlet box
Brand Name	Carlton
Type	Round Ceiling/Fixture Outlet Box with Bar Hanger
Material	Phenolic
Color	Brown
Mounting	N Bracket
Cubic Capacity	13.5 Cubic Inches

### European Specifications (ETIM)

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Round
Construction type	Device connection box (round/square)
Equipped with	Mounting plate
Diameter	88.9mm
Depth	-mm
Mounting switching equipment	Screwing
Pipe locking	N
Pipe locking optional	N
Surface protection	Other
Cover	None
Cover attachment	Not applicable

### Packaging

Outer Quantity	50
Outer Dimensions (inches)	21.68x12.5x12
Weight Uom	45.5 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)