



OPEN END HEADS - METRIC



Square Drive (mm)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.	X (0.735")	Max Torque Ft. Lbs.	Z (0.990")	Max Torque Ft. Lbs.	Z Dual Pins	Max Torque Ft. Lbs.
6	TCQJOM6A	5								
7	TCQJOM7A	6								
8	TCQJOM8A	10								
9	TCQJOM9A	14								
10	TCQJOM10A	22								
11	TCQJOM11A	33								
12	TCQJOM12A	36								
13	TCQJOM13A	41								
14	TCQJOM14A	55	TCQYOM14A	55						
15	TCQJOM15A	60	TCQYOM15A	74						
16	TCQJOM16A	60	TCQYOM16A	88						
17	TCQJOM17A	60	TCQYOM17A	103	TCQXOM17A	103				
18	TCQJOM18A	60	TCQYOM18A	115	TCQXOM18A	115				
19	TCQJOM19A	60	TCQYOM19A	138	TCQXOM19A	138				
20	TCQJOM20A	60	TCQYOM20A	160	TCQXOM20A	160				
21	TCQJOM21A	60	TCQYOM21A	160	TCQXOM21A	180				
22	TCQJOM22A	60	TCQYOM22A	160	TCQXOM22A	206				
23	TCQJOM23A	60	TCQYOM23A	160	TCQXOM23A	229				
24	TCQJOM24A	60	TCQYOM24A	160	TCQXOM24A	240	TCQZOM24A	248	TCQZOM24ADP	250
25	TCQJOM25A	60	TCQYOM25A	160	TCQXOM25A	240				
26	TCQJOM26A	60	TCQYOM26A	160	TCQXOM26A	240				
27	TCQJOM27A	60	TCQYOM27A	160	TCQXOM27A	240	TCQZOM27A	319	TCQZOM27ADP	319
29			TCQYOM29A	160	TCQXOM29A	240				
30	TCQJOM30	60	TCQYOM30A	160	TCQXOM30A	240	TCQZOM30A	413	TCQZOM30ADP	413
32			TCQYOM32A	160	TCQXOM32A	240	TCQZOM32A	480	TCQZOM32ADP	480
34			TCQYOM34A	160	TCQXOM34A	240			TCQZOM34ADP	480
36	TCQJOM36A	60	TCQYOM36A	160	TCQXOM36A	240	TCQZOM36A	480	TCQZOM36ADP	480
38									TCQZOM38ADP	480
41			TCQYOM41	160	TCQXOM41A	240			TCQZOM41ADP	480
46									TCQZOM46ADP	480
50							TCQZOM50A	480	TCQZOM50ADP	480
55							TCQZOM55A	480	TCQZOM55ADP	480
60									TCQZOM60ADP	480
65									TCQZOM65ADP	480
70									TCQZOM70ADP	480

TORQUE TOOLS

HEADS



OPEN END THIN HEADS - SAE

Square Drive (Inches)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.
11/16	TCQJO22ARTH60	60		
1	TCQJO32ARTH	60		
1 1/16	TCQJO34ARTH	60		
1 1/8	TCQJO36ARTH	60		
1 3/16	TCQJO38ARTH	60		
1 1/4	TCQJO40ARTH	60		
1 3/8	TCQJO44ARTH	60		
1 1/2	TCQJO48ARTH	60		
1 9/16	TCQJO50ARTH	60		
1 5/8	TCQJO52ARTH	60	TCQYO52ARTH	160
1 3/4	TCQJO56ARTH	60	TCQYO56ARTH	160
1 7/8	TCQJO60ARTH	60	TCQYO60ARTH	160
2	TCQJO64ARTH	60	TCQYO64ARTH	160
2 1/16	TCQJO66ARTH	60		
2 1/8			TCQYO68ARTH	160
2 1/4			TCQYO72ARTH	160
2 11/16	TCQJO86ARTH	60		



TCQJO38ARTH