

Deck Mounted, Single Hole Manual Faucet

- Hot and cold water mixing faucet
- 2.2 GPM (8.3 L/min) aerator
- 2-3/8" Vandal proof lever handle
- Polished chrome plated finish
- Quatern compression operating cartridge
- 3/8" Compression flexible stainless steel supply hoses



Spout	Model
6" S Type Swing	51-ABCP
8" L Type Swing	51-L8ABCP
12" L Type Swing	51-L12ABCP

Deck Mounted, 4" Fixed Centers, Manual Faucet

- Hot and cold water mixing faucet
- 2.2 GPM (8.3 L/min) aerator
- Quatern compression operating cartridge
- 1/2" NPSM supply inlets and coupling nut for 3/8" or 1/2" flexible riser
- Polished chrome plated finish
- Gooseneck spouts include rigid/swing option



Spout	Handle	Model
3-1/2" Gooseneck	Wristblade	895-317ABCP
5-1/4" Gooseneck		895-317GN2AE3ABCP
8" Gooseneck w/ Vacuum Breaker		895-317GN8BVBE2-2*
8" Gooseneck w/ Vacuum Breaker		895-317GN8BVBE3MAB
8" Gooseneck	Lever	895-GN8AE3ABCP

*Full-flow 3/4" male hose thread outlet

Deck Mounted, 8" Fixed Centers, Manual Faucet

- Concealed, hot and cold water faucet
- 2.2 GPM (8.3 L/min) aerator
- Quatern compression operating cartridge
- 1/2" NPSM supply inlets and coupling nut for 3/8" or 1/2" flexible riser
- Polished chrome plated finish
- Gooseneck spouts include rigid/swing option



Spout	Handle	Model
9-1/2" L Type Swing	Wristblade	201-A317ABCP
8" Gooseneck w/ Vacuum Breaker		201-AG8BVBE3M317AB
5-1/4" Gooseneck		786-E3ABCP
6" Gooseneck w/ Vacuum Breaker		786-GN2BVBE3-2ABCP
8" Gooseneck		786-GN8AE3ABCP
9-1/2" L Type Swing	Lever	201-AABCP
9-1/2" L Type Swing	Canopy	201-A1000ABCP