

drill diameter		decimal equivalent	overall length	flute length	order number	
frac/wire/let	mm				1603 Straw Oxide	1802 Straw Oxide
C		.2420	4	2-3/4	C68378	C23322
D		.2460	4	2-3/4	C68379	C23323
1/4, E		.2500	4	2-3/4	C68359	C23357
	6.50	.2559	101	63	—	C18955
F		.2570	4-1/8	2-7/8	C68380	C23324
G		.2610	4-1/8	2-7/8	C68381	C23325
17/64		.2656	4-1/8	2-7/8	C68360	C23358
H		.2660	4-1/8	2-7/8	C68382	C23326
	6.80	.2677	109	69	—	C18958
I		.2720	4-1/8	2-7/8	C68383	C23327
	7.00	.2756	109	69	—	C18960
J		.2770	4-1/8	2-7/8	C68384	C23328
K		.2810	4-1/4	2-15/16	C68385	C23329
9/32		.2812	4-1/4	2-15/16	C68361	C23359
L		.2900	4-1/4	2-15/16	C68386	C23330
M		.2950	4-3/8	3-1/16	C68387	—
	7.50	.2953	109	69	—	C18965
19/64		.2969	4-3/8	3-1/16	C68362	C23360
N		.3020	4-3/8	3-1/16	C68388	—
5/16		.3125	4-1/2	3-3/16	C68363	C23361
	8.00	.3150	117	75	—	C18970
O		.3160	4-1/2	3-3/16	C68389	—
P		.3230	4-5/8	3-5/16	C68390	—
21/64		.3281	4-5/8	3-5/16	C68364	C23362
Q		.3320	4-3/4	3-7/16	C68391	C23335
	8.50	.3346	117	75	—	C18975
R		.3390	4-3/4	3-7/16	C68392	C23336
11/32		.3438	4-3/4	3-7/16	C68365	C23363
S		.3480	4-7/8	3-1/2	C68393	—
	9.00	.3543	125	81	—	C18980
T		.3580	4-7/8	3-1/2	C68394	—
23/64		.3594	4-7/8	3-1/2	C68366	C23364
U		.3680	5	3-5/8	C68395	C23339
	9.50	.3740	125	81	—	C18985
3/8		.3750	5	3-5/8	C68367	C23365
V		.3770	5	3-5/8	C68396	C23340
W		.3860	5-1/8	3-3/4	C68397	C23341
25/64		.3906	5-1/8	3-3/4	C68368	C23366
	10.00	.3937	133	87	—	C18990
X		.3970	5-1/8	3-3/4	C68398	—
	10.20	.4016	133	87	—	C18991
Y		.4040	5-1/4	3-3/4	C68399	—
13/32		.4062	5-1/4	3-7/8	C68369	C23367
Z		.4130	5-1/4	3-7/8	C68400	—
	10.50	.4134	133	87	—	C18992
27/64		.4219	5-3/8	3-15/16	C68370	C23368
	11.00	.4331	142	94	—	C18993
7/16		.4375	5-1/2	4-1/16	C68371	C23369
	11.50	.4528	142	94	—	C18995
29/64		.4531	5-5/8	4-3/16	C68372	C23370
15/32		.4688	5-3/4	4-5/16	C68373	C23371
	12.00	.4724	151	101	—	C18996
31/64		.4844	5-7/8	4-3/8	C68374	C23372
	12.50	.4921	151	101	—	C18998
1/2		.5000	6	4-1/2	C68375	C23373
	13.00	.5118	151	101	—	C18999