

drill diameter		decimal equivalent	overall length	flute length	order number	
frac/wire/let	mm				1621 Black Oxide	1896 Black Oxide
34		.1110	1-7/8	7/8	—	C23526
33		.1130	1-7/8	7/8	—	C23527
32		.1160	1-7/8	7/8	—	C23528
	3.00	.1181	46	16	—	C23895
31		.1200	1-7/8	7/8	—	C23529
	3.10	.1220	49	18	—	C23896
1/8		.1250	1-7/8	7/8	C68495	C23464
	3.20	.1260	49	18	—	C23898
30		.1285	1-15/16	15/16	—	C23530
	3.30	.1299	49	18	—	C23899
	3.40	.1339	52	20	—	C23900
29		.1360	1-15/16	15/16	—	C23531
	3.50	.1378	52	20	—	C23901
28		.1405	1-15/16	15/16	—	C23532
9/64		.1406	1-15/16	15/16	C68496	C23465
	3.60	.1417	52	20	—	C24036
27		.1440	2-1/16	1	—	C23533
	3.70	.1457	52	20	—	C23902
26		.1470	2-1/16	1	—	C23534
25		.1495	2-1/16	1	—	C23535
	3.80	.1496	55	22	—	C23903
24		.1520	2-1/16	1	—	C23536
23		.1540	2-1/16	1	—	C23537
5/32		.1562	2-1/16	1	C68497	C23466
22		.1570	2-1/8	1-1/16	—	C23538
	4.00	.1575	55	22	—	C23904
21		.1590	2-1/8	1-1/16	—	C23539
20		.1610	2-1/8	1-1/16	—	C23540
	4.10	.1614	55	22	—	C23905
	4.20	.1654	55	22	—	C23906
19		.1660	2-1/8	1-1/16	—	C23541
	4.30	.1693	58	24	—	C23907
18		.1695	2-1/8	1-1/16	—	C23542
11/64		.1719	2-1/8	1-1/16	C68498	C23467
17		.1730	2-3/16	1-1/8	—	C23543
16		.1770	2-3/16	1-1/8	—	C23544
	4.50	.1772	58	24	—	C23908
15		.1800	2-3/16	1-1/8	—	C23545
	4.60	.1811	58	24	—	C23909
14		.1820	2-3/16	1-1/8	—	C23546
13		.1850	2-3/16	1-1/8	—	C23547
	4.70	.1850	58	24	—	C23910
3/16		.1875	2-3/16	1-1/8	C68499	C23468
12		.1890	2-1/4	1-3/16	—	C23548
	4.80	.1890	62	26	—	C23911
11		.1910	2-1/4	1-3/16	—	C23549
	4.90	.1929	62	26	—	C23912
10		.1935	2-1/4	1-3/16	—	C23550
9		.1960	2-1/4	1-3/16	—	C23551
	5.00	.1969	62	26	—	C23913
8		.1990	2-1/4	1-3/16	—	C23552

*continued on next page*