

## One-Piece Clamping Couplings-Recessed Screws - CC-Series



- Recessed screw head provides an outside surface free of major projections for safety
- Does not mar the shaft

DIMENSION Bore, Inch
TOLERANCE +.003/-000

Black Oxide Steel	Black Oxide Steel With Keyway	Bore Size	2nd Bore Size	OD	Length	Clamp Screw	Box Qty	Approx. Weight (oz.)
CC-025-025		1/4	1/4	13/16	1 1/4	4-40 x 3/8	5	2.26
CC-037-025		3/8	1/4	1 1/16	1 5/8	6-32 x 1/2	5	5.13
CC-037-037	CC-037-037-KW	3/8	3/8	1 1/16	1 5/8	6-32 x 3/8	5	4.96
CC-050-037		1/2	3/8	1 1/4	1 7/8	8-32 x 1/2	5	8.11
CC-050-050	CC-050-050-KW	1/2	1/2	1 1/4	1 7/8	8-32 x 1/2	5	7.70
CC-062-050		5/8	1/2	1 1/2	2 1/4	10-32 x 1/2	5	13.30
CC-062-062	CC-062-062-KW	5/8	5/8	1 1/2	2 1/4	10-32 x 1/2	5	13.30
CC-075-050		3/4	1/2	1 3/4	2 5/8	1/4-28 x 5/8	5	22.00
CC-075-062		3/4	5/8	1 3/4	2 5/8	1/4-28 x 5/8	5	22.00
CC-075-075	CC-075-075-KW	3/4	3/4	1 3/4	2 5/8	1/4-28 x 5/8	5	20.90
CC-087-062		7/8	5/8	1 7/8	2 7/8	1/4-28 x 5/8	2	27.40
CC-087-087	CC-087-087-KW	7/8	7/8	1 7/8	2 7/8	1/4-28 x 5/8	2	25.40
CC-100-050		1	1/2	2	3	1/4-28 x 5/8	2	32.80
CC-100-075		1	3/4	2	3	1/4-28 x 5/8	2	31.40
CC-100-100	CC-100-100-KW	1	1	2	3	1/4-28 x 5/8	2	29.00
CC-112-100		1 1/8	1	2 1/8	3 1/4	1/4-28 x 3/4	2	35.90
CC-112-112	CC-112-112-KW	1 1/8	1 1/8	2 1/8	3 1/4	1/4-28 x 3/4	2	34.70
CC-125-100		1 1/4	1	2 1/8	3 3/8	1/4-28 x 3/4	2	41.80
CC-125-125	CC-125-125-KW	1 1/4	1 1/4	2 1/4	3 3/8	1/4-28 x 3/4	2	38.40
CC-137-100		1 3/8	1	2 3/8	3 5/8	1/4-28 x 3/4	2	50.00
CC-137-137	CC-137-137-KW	1 3/8	1 3/8	2 3/8	3 5/8	1/4-28 x 3/4	2	44.70
CC-150-100		1 1/2	1	2 1/2	3 3/4	1/4-28 x 3/4	1	57.40
CC-150-150	CC-150-150-KW	1 1/2	1 1/2	2 1/2	3 3/4	1/4-28 x 3/4	1	49.50
CC-175-175	CC-175-175-KW	1 3/4	1 3/4	3	4 1/2	5/16-24 x 1	1	90.00
CC-200-200	CC-200-200-KW	2	2	3 1/4	4 7/8	5/16-24 x 1	1	107.00
CC-225-225	CC-225-225-KW	2 1/4	2 1/4	3 1/2	5	5/16-24 x 1	1	130.00

## Two-Piece Clamping Couplings-Recessed Screws - 2CC-Series



- Recessed screw head provides an outside surface free of major projections for safety
- Easily installed where major disassembly would otherwise be required
- Does not mar the shaft

Black Oxide Steel	Black Oxide Steel With Keyway	Bore Size	2nd Bore Size	OD	Length	Clamp Screw	Box Qty	Approx. Weight (oz.)
2CC-025-025		1/4	1/4	13/16	1 1/4	4-40 x 3/8	5	2.26
2CC-037-025		3/8	1/4	1 1/16	1 5/8	6-32 x 1/2	5	5.13
2CC-037-037	2CC-037-037-KW	3/8	3/8	1 1/16	1 5/8	6-32 x 3/8	5	4.96
2CC-050-037	2CC-050-037-KW	1/2	3/8	1 1/4	1 7/8	8-32 x 1/2	5	8.11
2CC-050-050	2CC-050-050-KW	1/2	1/2	1 1/4	1 7/8	8-32 x 1/2	5	7.90
2CC-062-050	2CC-062-050-KW	5/8	1/2	1 1/2	2 1/4	10-32 x 1/2	5	13.60
2CC-062-062	2CC-062-062-KW	5/8	5/8	1 1/2	2 1/4	10-32 x 1/2	5	22.50
2CC-075-050	2CC-075-050-KW	3/4	1/2	1 3/4	2 5/8	1/4-28 x 5/8	5	22.00
2CC-075-062	2CC-075-062-KW	3/4	5/8	1 3/4	2 5/8	1/4-28 x 5/8	5	22.00
2CC-075-075	2CC-075-075-KW	3/4	3/4	1 3/4	2 5/8	1/4-28 x 5/8	5	22.00
2CC-087-062	2CC-087-062KW	7/8	5/8	1 7/8	2 7/8	1/4-28 x 5/8	2	27.40
2CC-087-087	2CC-087-087-KW	7/8	7/8	1 7/8	2 7/8	1/4-28 x 5/8	2	26.00
2CC-100-050	2CC-100-050-KW	1	1/2	2	3	1/4-28 x 5/8	2	27.40
2CC-100-075	2CC-100-075-KW	1	3/4	2	3	1/4-28 x 5/8	2	29.10
2CC-100-100	2CC-100-100-KW	1	1	2	3	1/4-28 x 5/8	2	29.10
2CC-112-100	2CC-112-100-KW	1 1/8	1	2 1/8	3 1/4	1/4-28 x 3/4	2	35.90
2CC-112-112	2CC-112-112-KW	1 1/8	1 1/8	2 1/8	3 1/4	1/4-28 x 3/4	2	34.20
2CC-125-100	2CC-125-100-KW	1 1/4	1	2 1/4	3 3/8	1/4-28 x 3/4	2	42.40
2CC-125-125	2CC-125-125-KW	1 1/4	1 1/4	2 1/4	3 3/8	1/4-28 x 3/4	2	42.40
2CC-137-100	2CC-137-100-KW	1 3/8	1	2 3/8	3 5/8	1/4-28 x 3/4	2	45.20
2CC-137-137	2CC-137-137-KW	1 3/8	1 3/8	2 3/8	3 5/8	1/4-28 x 3/4	2	45.20
2CC-150-100	2CC-150-100-KW	1 1/2	1	2 1/2	3 3/4	1/4-28 x 3/4	1	57.40
2CC-150-150	2CC-150-150-KW	1 1/2	1 1/2	2 1/2	3 3/4	1/4-28 x 3/4	1	49.50
2CC-175-175	2CC-175-175-KW	1 3/4	1 3/4	3	4 1/2	5/16-24 x 1	1	90.00
2CC-200-200	2CC-200-200-KW	2	2	3 1/4	4 7/8	5/16-24 x 1	1	110.00
2CC-225-225	2CC-225-225-KW	2 1/4	2 1/4	3 1/2	5	5/16-24 x 1	1	130.00