

Two-Piece Clamping Collars - 2C-Series

Black Oxide Steel	Stainless Steel	Zinc Plated Aluminum	Zinc Plated Steel	Yellow Zinc Dichromate	316 Stainless Steel	Bore Size	OD	Width	Clamp Screw	Box Qty	Approx. Weight (oz.)
2C-012	2C-012-S	2C-012-A	2C-012-Z			1/8	11/16	5/16	4-40 x 3/8	20	0.43
2C-018	2C-018-S	2C-018-A	2C-018-Z			3/16	11/16	5/16	4-40 x 3/8	20	0.39
2C-025	2C-025-S	2C-025-A	2C-025-Z			1/4	11/16	5/16	4-40 x 3/8	20	0.38
2C-031	2C-031-S	2C-031-A	2C-031-Z			5/16	11/16	5/16	4-40 x 3/8	20	0.34
2C-037	2C-037-S	2C-037-A	2C-037-Z			3/8	7/8	3/8	6-32 x 3/8	20	0.71
2C-043	2C-043-S	2C-043-A	2C-043-Z			7/16	15/16	3/8	6-32 x 3/8	20	0.76
2C-050	2C-050-S	2C-050-A	2C-050-Z	CR2C-050	CR2C-050-S	1/2	1 1/8	13/32	8-32 x 1/2	20	1.26
2C-056	2C-056-S	2C-056-A	2C-056-Z			9/16	1 5/16	7/16	10-32 x 1/2	20	2.00
2C-062	2C-062-S	2C-062-A	2C-062-Z	CR2C-062	CR2C-062-S	5/8	1 5/16	7/16	10-32 x 1/2	20	1.80
2C-068	2C-068-S	2C-068-A	2C-068-Z			11/16	1 1/2	1/2	10-32 x 1/2	20	2.80
2C-075	2C-075-S	2C-075-A	2C-075-Z	CR2C-075	CR2C-075-S	3/4	1 1/2	1/2	1/4-28 x 5/8	20	2.60
2C-081	2C-081-S	2C-081-A	2C-081-Z			13/16	1 5/8	1/2	1/4-28 x 5/8	20	3.10
2C-087	2C-087-S	2C-087-A	2C-087-Z			7/8	1 5/8	1/2	1/4-28 x 5/8	20	2.83
2C-093	2C-093-S	2C-093-A	2C-093-Z			15/16	1 3/4	1/2	1/4-28 x 5/8	20	3.40
2C-100	2C-100-S	2C-100-A	2C-100-Z	CR2C-100	CR2C-100-S	1	1 3/4	1/2	1/4-28 x 5/8	20	3.10
2C-106	2C-106-S	2C-106-A	2C-106-Z			1 1/16	1 7/8	1/2	1/4-28 x 5/8	10	3.67
2C-112	2C-112-S	2C-112-A	2C-112-Z			1 1/8	1 7/8	1/2	1/4-28 x 3/4	10	3.50
2C-118	2C-118-S	2C-118-A	2C-118-Z			1 3/16	2 1/16	1/2	1/4-28 x 3/4	10	4.50
2C-125	2C-125-S	2C-125-A	2C-125-Z	CR2C-125	CR2C-125-S	1 1/4	2 1/16	1/2	1/4-28 x 3/4	10	4.22
2C-131	2C-131-S	2C-131-A	2C-131-Z			1 5/16	2 1/4	9/16	1/4-28 x 3/4	10	5.90
2C-137	2C-137-S	2C-137-A	2C-137-Z			1 3/8	2 1/4	9/16	1/4-28 x 3/4	10	5.70
2C-143	2C-143-S	2C-143-A	2C-143-Z			1 7/16	2 1/4	9/16	1/4-28 x 3/4	10	5.23
2C-150	2C-150-S	2C-150-A	2C-150-Z			1 1/2	2 3/8	9/16	1/4-28 x 3/4	10	6.06
2C-156	2C-156-S	2C-156-A	2C-156-Z			1 9/16	2 3/8	9/16	1/4-28 x 3/4	10	5.61
2C-162	2C-162-S	2C-162-A	2C-162-Z			1 5/8	2 5/8	11/16	5/16-24 x 1	5	9.31
2C-168	2C-168-S	2C-168-A	2C-168-Z			1 11/16	2 3/4	11/16	5/16-24 x 1	5	9.86
2C-175	2C-175-S	2C-175-A	2C-175-Z			1 3/4	2 3/4	11/16	5/16-24 x 1	5	11.00
2C-181	2C-181-S	2C-181-A	2C-181-Z			1 13/16	2 7/8	11/16	5/16-24 x 1	5	10.90
2C-187	2C-187-S	2C-187-A	2C-187-Z			1 7/8	2 7/8	11/16	5/16-24 x 1	5	10.46
2C-193	2C-193-S	2C-193-A	2C-193-Z			1 15/16	3	11/16	5/16-24 x 1	5	11.57
2C-200	2C-200-S	2C-200-A	2C-200-Z			2	3	11/16	5/16-24 x 1	5	11.00
2C-206	2C-206-S	2C-206-A	2C-206-Z			2 1/16	3 1/4	3/4	5/16-24 x 1	5	11.00
2C-212	2C-212-S	2C-212-A	2C-212-Z			2 1/8	3 1/4	3/4	5/16-24 x 1	5	15.00
2C-218	2C-218-S	2C-218-A	2C-218-Z			2 3/16	3 1/4	3/4	5/16-24 x 1	5	14.00
2C-225	2C-225-S	2C-225-A	2C-225-Z			2 1/4	3 1/4	3/4	5/16-24 x 1	5	13.10
2C-231	2C-231-S	2C-231-A	2C-231-Z			2 5/16	3 1/2	3/4	5/16-24 x 1	5	15.90
2C-237	2C-237-S	2C-237-A	2C-237-Z			2 3/8	3 1/2	3/4	5/16-24 x 1	5	15.20
2C-243	2C-243-S	2C-243-A	2C-243-Z			2 7/16	3 1/2	3/4	5/16-24 x 1	5	15.30
2C-250	2C-250-S	2C-250-A	2C-250-Z			2 1/2	3 3/4	7/8	3/8-24 x 1	5	22.30
2C-256	2C-256-S	2C-256-A	2C-256-Z			2 9/16	3 7/8	7/8	3/8-24 x 1	5	24.00
2C-262	2C-262-S	2C-262-A	2C-262-Z			2 5/8	3 7/8	7/8	3/8-24 x 1	5	24.00
2C-268	2C-268-S	2C-268-A	2C-268-Z			2 11/16	4	7/8	3/8-24 x 1	5	25.00
2C-275	2C-275-S	2C-275-A	2C-275-Z			2 3/4	4	7/8	3/8-24 x 1	5	24.00
2C-281	2C-281-S	2C-281-A	2C-281-Z			2 13/16	4 1/4	7/8	3/8-24 x 1	5	29.20
2C-287	2C-287-S	2C-287-A	2C-287-Z			2 7/8	4 1/4	7/8	3/8-24 x 1	5	29.00
2C-293	2C-293-S	2C-293-A	2C-293-Z			2 15/16	4 1/4	7/8	3/8-24 x 1	5	26.50
2C-300	2C-300-S	2C-300-A	2C-300-Z			3	4 1/4	7/8	3/8-24 x 1	5	25.80
H2C-318	H2C-318-S					3 3/16	4 1/2	7/8	3/8-24 x 1	5	28.30
H2C-325	H2C-325-S					3 1/4	4 1/2	7/8	3/8-24 x 1	5	27.30
H2C-337	H2C-337-S					3 3/8	4 3/4	7/8	3/8-24 x 1	5	29.00
H2C-343	H2C-343-S					3 7/16	4 3/4	7/8	3/8-24 x 1	5	31.00
H2C-350	H2C-350-S					3 1/2	4 3/4	7/8	3/8-24 x 1	5	29.10
H2C-375	H2C-375-S					3 3/4	5	7/8	3/8-24 x 1	5	32.00
H2C-393	H2C-393-S					3 15/16	5 1/4	7/8	3/8-24 x 1	5	35.00
H2C-400	H2C-400-S					4	5 1/4	7/8	3/8-24 x 1	5	33.00
H2C-425	H2C-425-S					4 1/4	5 1/2	7/8	3/8-24 x 1	5	35.00
H2C-443	H2C-443-S					4 7/16	5 3/4	7/8	3/8-24 x 1	5	38.50
H2C-450	H2C-450-S					4 1/2	5 3/4	7/8	3/8-24 x 1	5	36.00
H2C-493	H2C-493-S					4 15/16	6 1/4	7/8	3/8-24 x 1	5	42.50
H2C-500	H2C-500-S					5	6 1/4	7/8	3/8-24 x 1	5	40.10
H2C-525	H2C-525-S					5 1/4	6 3/4	7/8	3/8-24 x 1	5	42.00
H2C-550	H2C-550-S					5 1/2	6 3/4	7/8	3/8-24 x 1	5	43.30
H2C-593	H2C-593-S					5 15/16	7 1/4	7/8	3/8-24 x 1	1	50.30
H2C-600	H2C-600-S					6	7 1/4	7/8	3/8-24 x 1	1	47.60



- Design fully engages the shaft without marring
- Effective on hard and soft shafts
- Easily installed where major disassembly would otherwise be required
- Greater axial holding power than set screw or one-piece clamping collars

DIMENSION
Bore, Inch

TOLERANCE
+.003/-.000

* Zinc plated clamping collars come with stainless steel screws.
 * Screw lengths are for steel only.
 * H2C-318 and larger do not have recessed screws (Steel and Stainless Steel).