

### One-Piece Industry Standard Clamping Couplings - ISCC-Series



- High axial load and torque capacity
- Does not mar the shaft

Black Oxide Steel	Stainless Steel	Aluminum	Bore Size	2nd Bore Size	OD	Length	Clamp Screw	Box Qty	Approx. Weight (oz.)
ISCC-025-025	ISCC-025-025-S	ISCC-025-025-A	1/4	1/4	11/16	1 1/8	4-40 x 3/8	10	1.50
ISCC-037-025	ISCC-037-025-S		3/8	1/4	7/8	1 3/8	6-32 x 3/8	10	2.70
ISCC-037-037	ISCC-037-037-S	ISCC-037-037-A	3/8	3/8	7/8	1 3/8	6-32 x 3/8	5	2.60
ISCC-050-037	ISCC-050-037-S		1/2	3/8	1 1/8	1 3/4	8-32 x 1/2	5	6.00
ISCC-050-050	ISCC-050-050-S	ISCC-050-050-A	1/2	1/2	1 1/8	1 3/4	8-32 x 1/2	5	5.70
ISCC-062-050	ISCC-062-050-S		5/8	1/2	1 5/16	2	10-32 x 1/2	5	9.00
ISCC-062-062	ISCC-062-062-S		5/8	5/8	1 5/16	2	10-32 x 1/2	5	8.50
ISCC-075-050	ISCC-075-050-S		3/4	1/2	1 1/2	2 1/4	1/4-28 x 5/8	5	12.20
ISCC-075-062	ISCC-075-062-S		3/4	5/8	1 1/2	2 1/4	1/4-28 x 5/8	5	12.20
ISCC-075-075	ISCC-075-075-S		3/4	3/4	1 1/2	2 1/4	1/4-28 x 5/8	5	12.20
ISCC-087-062	ISCC-087-062-S		7/8	5/8	1 5/8	2 1/2	1/4-28 x 5/8	5	15.40
ISCC-087-087	ISCC-087-087-S		7/8	7/8	1 5/8	2 1/2	1/4-28 x 5/8	5	15.40
ISCC-100-050	ISCC-100-050-S		1	1/2	1 3/4	3	1/4-28 x 5/8	2	23.60
ISCC-100-075	ISCC-100-075-S		1	3/4	1 3/4	3	1/4-28 x 5/8	2	20.00
ISCC-100-100	ISCC-100-100-S		1	1	1 3/4	3	1/4-28 x 5/8	2	20.00
ISCC-112-100	ISCC-112-100-S		1 1/8	1	1 7/8	3 1/8	1/4-28 x 5/8	2	22.00
ISCC-112-112	ISCC-112-112-S		1 1/8	1 1/8	1 7/8	3 1/8	1/4-28 x 5/8	2	22.00
ISCC-125-100	ISCC-125-100-S		1 1/4	1	2 1/16	3 1/4	1/4-28 x 3/4	2	28.40
ISCC-125-125	ISCC-125-125-S		1 1/4	1 1/4	2 1/16	3 1/4	1/4-28 x 3/4	2	28.40
ISCC-137-100	ISCC-137-100-S		1 3/8	1	2 1/4	3 1/2	1/4-28 x 3/4	2	37.00
ISCC-137-137	ISCC-137-137-S		1 3/8	1 3/8	2 1/4	3 1/2	1/4-28 x 3/4	2	37.00
ISCC-150-100	ISCC-150-100-S		1 1/2	1	2 5/8	3 7/8	5/16-24 x 1	1	49.50
ISCC-150-150	ISCC-150-150-S		1 1/2	1 1/2	2 5/8	3 7/8	5/16-24 x 1	1	49.50
ISCC-175-175	ISCC-175-175-S		1 3/4	1 3/4	3 1/8	4 1/2	3/8-24 x 1	1	102.30
ISCC-200-200	ISCC-200-200-S		2	2	3 3/8	4 7/8	3/8-24 x 1	1	107.00



Black Oxide Steel With Keyway	Stainless Steel With Keyway	Bore Size	2nd Bore Size	OD	Length	Clamp Screw	Box Qty	Approx. Weight (oz.)
ISCC-037-037-KW	ISCC-037-037SKW	3/8	3/8	7/8	1 3/8	6-32 x 3/8	5	2.60
ISCC-050-050-KW	ISCC-050-050SKW	1/2	1/2	1 1/8	1 3/4	8-32 x 1/2	5	5.70
ISCC-062-062-KW	ISCC-062-062SKW	5/8	5/8	1 5/16	2	10-32 x 1/2	5	8.50
ISCC-075-075-KW	ISCC-075-075SKW	3/4	3/4	1 1/2	2 1/4	1/4-28 x 5/8	5	12.20
ISCC-087-087-KW	ISCC-087-087SKW	7/8	7/8	1 5/8	2 1/2	1/4-28 x 5/8	5	15.40
ISCC-100-100-KW	ISCC-100-100SKW	1	1	1 3/4	3	1/4-28 x 5/8	2	20.00
ISCC-112-112-KW	ISCC-112-112SKW	1 1/8	1 1/8	1 7/8	3 1/8	1/4-28 x 5/8	2	22.00
ISCC-125-125-KW	ISCC-125-125SKW	1 1/4	1 1/4	2 1/16	3 1/4	1/4-28 x 5/8	2	28.40
ISCC-137-137-KW	ISCC-137-137SKW	1 3/8	1 3/8	2 1/4	3 1/2	1/4-28 x 3/4	2	37.00
ISCC-150-150-KW	ISCC-150-150SKW	1 1/2	1 1/2	2 5/8	3 7/8	5/16-24 x 1	1	49.50
ISCC-175-175-KW	ISCC-175-175SKW	1 3/4	1 3/4	3 1/8	4 1/2	3/8-24 x 1	1	102.30
ISCC-200-200-KW	ISCC-200-200SKW	2	2	3 3/8	4 7/8	3/8-24 x 1	1	107.00

DIMENSION  
Bore, Inch

TOLERANCE  
+.003/-.000