

<b>Model</b>	<b>Top Inlet Connection</b>	<b>Side Inlet Connection</b>	<b>Outlet Connection</b>
<b>NG-1</b>	1/2" (-8) FEMALE NPT 1/2-14 NPT	NONE OR P1/P2 OPTION	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-2</b>	NONE OR P1/P2 OPTION	1/2" (-8) FEMALE NPT 1/2-14 NPT	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-3</b>	1/2" (-8) COMPRESSION 11/16-20 UN-2A	NONE OR P1/P2 OPTION	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-4</b>	NONE OR P1/P2 OPTION	1/2" (-8) COMPRESSION 11/16-20 UN-2A	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-5</b>	1/2" (-8) FEMALE NPT 1/2-14 NPT	NONE OR P1/P2 OPTION	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-6</b>	NONE OR P1/P2 OPTION	1/2" (-8) FEMALE NPT 1/2-14 NPT	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-7</b>	1/2" (-8) COMPRESSION 11/16-20 UN-2A	NONE OR P1/P2 OPTION	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-8</b>	NONE OR P1/P2 OPTION	1/2" (-8) COMPRESSION 11/16-20 UN-2A	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-9</b>	5/8" (-10) COMPRESSION 13/16-18 UN-2A	NONE OR P1/P2 OPTION	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-10</b>	NONE OR P1/P2 OPTION	5/8" (-10) COMPRESSION 13/16-18 UN-2A	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-11</b>	5/8" (-10) COMPRESSION 13/16-18 UN-2A	NONE OR P1/P2 OPTION	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-12</b>	NONE OR P1/P2 OPTION	5/8" (-10) COMPRESSION 13/16-18 UN-2A	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-13</b>	5/8" (-10) INVERTED SAE FLARE 7/8-18 UNS-2B	NONE OR P1/P2 OPTION	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-14</b>	NONE OR P1/P2 OPTION	5/8" (-10) INVERTED SAE FLARE 7/8-18 UNS-2B	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-15</b>	5/8" (-10) INVERTED SAE FLARE 7/8-18 UNS-2B	NONE OR P1/P2 OPTION	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-16</b>	NONE OR P1/P2 OPTION	5/8" (-10) INVERTED SAE FLARE 7/8-18 UNS-2B	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-17</b>	3/4" (-12) COMPRESSION 1-18 UNS-2A	NONE OR P1/P2 OPTION	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-18</b>	NONE OR P1/P2 OPTION	3/4" (-12) COMPRESSION 1-18 UNS-2A	1/2" (-8) FEMALE NPT 1/2-14 NPT
<b>NG-19</b>	3/4" (-12) COMPRESSION 1-18 UNS-2A	NONE OR P1/P2 OPTION	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-20</b>	NONE OR P1/P2 OPTION	3/4" (-12) COMPRESSION 1-18 UNS-2A	1/2" (-8) MALE NPT 1/2-14 NPT
<b>NG-21</b>	1/2" (-8) FEMALE NPT 1/2-14 NPT	NONE OR P1/P2 OPTION	3/8" (-6) MALE NPT 3/8-18 NPT
<b>NG-22</b>	NONE OR P1/P2 OPTION	1/4" (-4) FEMALE NPT 1/4-18 NPT	1/4" (-4) FEMALE NPT 1/4-18 NPT