



- BC442 fits beam flanges  $\frac{1}{8}$ " to  $\frac{5}{8}$ ". BC442-6 fits beam flanges up to  $\frac{3}{4}$ ".
- Finish: Zinc Plated.
- Static Load Capacity:  
BC442 = 100 Lbs.  
BC442-6 = 200 Lbs.

## Beam Fasteners



UPC/Part Number	Catalog Number	Description	Box Qty.
78101118278	<b>BC442</b>	Accepts $\frac{1}{4}$ "-20 Threaded Rod or $\frac{1}{4}$ "-20 Threaded Bridle Rings	50
78101104283	<b>BC442-6</b>	Accepts $\frac{3}{8}$ "-16 Threaded Rod	25



UPC/Part Number	Catalog Number	Conduit Size Rigid	EMT	Box Qty.
78101119850	<b>BL1400-C442</b>	$\frac{1}{2}$ "	$\frac{1}{2}$ "	50
78101119851	<b>BL1410-C442</b>	$\frac{3}{4}$ "	$\frac{3}{4}$ "	50
78101119852	<b>BL1420-C442</b>	1"	1"	50
78101119853	<b>BL1425-C442</b>	--	1 $\frac{1}{4}$ "	50
78101119854	<b>BL1430-C442</b>	1 $\frac{1}{4}$ "	1 $\frac{1}{2}$ "	50
78101119855	<b>BL1440-C442</b>	1 $\frac{1}{2}$ "	--	25
78101119856	<b>BL1450-C442</b>	2"	2"	25

Read safety/installation instruction sheets in packages before use. These products are designed for positioning only. No load rating.