



Push-Type Conduit & Box Support Fasteners

- Consult factory for pre-fab box assemblies.

- BMC3 plate is available to support multiple conduit runs.
- Riveted assembly secures electrical boxes and conduit runs to beam flanges $\frac{1}{8}$ " to $\frac{1}{2}$ " thick.
- Provides support for conduit on either side of electrical box.
- Assemblies using BMC3 plate include center conduit clamp. Additional conduit clamps may be purchased separately.



BP__-S18-U__



BP__-S18-U__-MC3

UPC/Part Number	Catalog Number	Conduit Size EMT, IMC, Rigid	Flange Thickness	Box Qty.
78205123635	BP8-S18-U24	$\frac{3}{8}$ "	$\frac{1}{8}$ " to $\frac{1}{4}$ "	25
78205123638	BP8-S18-U58	$\frac{3}{8}$ "	$\frac{5}{16}$ " to $\frac{1}{2}$ "	25
78205123636	BP12-S18-U24	$\frac{1}{2}$ ", $\frac{3}{4}$ "	$\frac{1}{8}$ " to $\frac{1}{4}$ "	25
78205123639	BP12-S18-U58	$\frac{1}{2}$ ", $\frac{3}{4}$ "	$\frac{5}{16}$ " to $\frac{1}{2}$ "	25
78205123637	BP16-S18-U24	1"	$\frac{1}{8}$ " to $\frac{1}{4}$ "	25
78205123640	BP16-S18-U58	1"	$\frac{5}{16}$ " to $\frac{1}{2}$ "	25

Patent #4958792

With Multiple Conduit Plate

78205152824	BP8-S18-U24-MC3	$\frac{3}{8}$ "	$\frac{1}{8}$ " to $\frac{1}{4}$ "	25
78205152825	BP8-S18-U58-MC3	$\frac{3}{8}$ "	$\frac{5}{16}$ " to $\frac{1}{2}$ "	25
78205152827	BP12-S18-U24-MC3	$\frac{1}{2}$ ", $\frac{3}{4}$ "	$\frac{1}{8}$ " to $\frac{1}{4}$ "	25
78205152828	BP12-S18-U58-MC3	$\frac{1}{2}$ ", $\frac{3}{4}$ "	$\frac{5}{16}$ " to $\frac{1}{2}$ "	25
78205152825	BP16-S18-U24-MC3	1"	$\frac{1}{8}$ " to $\frac{1}{4}$ "	25
78205152964	BP16-S18-U58-MC3	1"	$\frac{5}{16}$ " to $\frac{1}{2}$ "	25

Read safety/installation instruction sheets in packages before use.
These products are designed for positioning only. No load rating.