

DURA-BLOK rooftop supports

Support Bases Only

- Base only - see chart for height, width and length.
- 100% recycled rubber, UV resistant.
- Load Rating - Ultimate Uniform Load (See Chart Below)*
- DURA-BLOK channel support is designed as an economical support for piping systems, cable tray, HVAC equipment and many other applications. The DURA-BLOK is UV resistant and suitable for any type of roofing material or other flat surfaces. Material effectively accepts screw fasteners for securing accessories.



DBM



DBP

Part No.	Height x Width x Length In. mm	Wt./Each Lbs. kg	Load Rating Lbs. kN
DBM	4" x 6" x 4.8" (101.6 x 152.4 x 121.9)	2.35 (1.07)	200 (0.89)
DBP	4" x 6" x 9.6" (101.6 x 152.4 x 243.8)	4.48 (2.03)	500 (2.22)

DB Series - Support Bases with Channel

- Base with 1" (25.4mm) tall galvanized channel - see chart for overall height, width and length.
- 100% recycled rubber, UV resistant.
- Load Rating - Ultimate Uniform Load (See Chart Below)*
- DURA-BLOK DB-Series channel support is designed for superior support of piping systems, cable tray, HVAC equipment, walkway systems and many other applications. The DURA-BLOK is UV resistant and suitable for installation on any type of roofing material or other flat surfaces. (For pipe straps/clamps, rollers and roller supports that can be used with these DURA-BLOK supports, see page 202)
- For sloped roofs use B634 adjustable hinge fittings (see page 118).



DB10



DB20



DB30

Part No.	Height x Width x Length In. mm	Wt./Each Lbs. kg	Load Rating Lbs. kN
DB5	5" x 6" x 4.8" (127.0 x 152.4 x 121.9)	2.75 (1.25)	200 (0.89)
DB10	5" x 6" x 9.6" (127.0 x 152.4 x 243.8)	5.28 (2.39)	500 (2.22)
DB20	5" x 6" x 20.2" (127.0 x 152.4 x 513.1)	10.63 (4.82)	1000 (4.45)
DB30	5" x 6" x 30.8" (127.0 x 152.4 x 782.3)	15.99 (7.25)	1500 (6.67)
DB40	5" x 6" x 41.4" (127.0 x 152.4 x 1051.5)	21.34 (9.68)	2000 (8.89)
DB48	5" x 6" x 52.0" (127.0 x 152.4 x 1320.8)	26.70 (12.40)	2500 (11.12)

DB6 Series - Support Base with B12 Channel

- Base with 12 ga. (2.6mm) galvanized channel 27/16" (61.9mm) tall - see chart for overall height, width and length.
- 100% recycled rubber, UV resistant.
- Load Rating - Ultimate Uniform Load (See Chart Below)*
- DURA-BLOK DB-Series channel support is designed for superior support of piping systems, cable tray, HVAC equipment, walkway systems and many other applications. The DURA-BLOK is UV resistant and suitable for installation on any type of roofing material or other flat surfaces. (For pipe straps/clamps, rollers and roller supports that can be used with these DURA-BLOK supports, see page 202)
- For sloped roofs use B634 adjustable hinge fittings (see page 118).



DB610



DB620



DB630

Part No.	Height x Width x Length In. mm	Wt./Each Lbs. kg	Load Rating Lbs. kN
DB610	67/16" x 6" x 9.6" (163.5 x 152.4 x 243.8)	6.36 (2.88)	500 (2.22)
DB620	67/16" x 6" x 20.2" (163.5 x 152.4 x 513.1)	12.90 (5.85)	1000 (4.45)
DB630	67/16" x 6" x 30.8" (163.5 x 152.4 x 782.3)	19.45 (8.82)	1500 (6.67)
DB640	67/16" x 6" x 41.4" (163.5 x 152.4 x 1051.5)	26.00 (11.79)	2000 (8.89)
DB648	67/16" x 6" x 52.0" (163.5 x 152.4 x 1320.8)	32.55 (14.76)	2500 (11.12)

* **General Note:** Consult roofing manufacturer or engineer for roof load capacity. The weakest point may be the insulation board beneath the rubber membrane.

DURA-BLOK Supports

Reference page 196 for general fitting and standard finish specifications.