

# DURA-BLOK rooftop supports

DB\_DS Series cont.

Part No.	A Min. to Max.		B	
	In.	mm	In.	mm
<b>DB2318DS</b>	10.56"	20.75" (268 to 527)	13 <sup>1</sup> / <sub>2</sub> "	(343)
<b>DB2918DS</b>	10.56"	26.75" (268 to 679)	13 <sup>1</sup> / <sub>2</sub> "	(343)
<b>DB4118DS</b>	10.56"	38.75" (268 to 984)	13 <sup>1</sup> / <sub>2</sub> "	(343)
<b>DB5318DS</b>	10.56"	50.75" (268 to 1289)	13 <sup>1</sup> / <sub>2</sub> "	(343)
<b>DB2324DS</b>	10.56"	20.75" (268 to 527)	19 <sup>1</sup> / <sub>2</sub> "	(495)
<b>DB2924DS</b>	10.56"	26.75" (268 to 679)	19 <sup>1</sup> / <sub>2</sub> "	(495)
<b>DB4124DS</b>	10.56"	38.75" (268 to 984)	19 <sup>1</sup> / <sub>2</sub> "	(495)
<b>DB5324DS</b>	10.56"	50.75" (268 to 1289)	19 <sup>1</sup> / <sub>2</sub> "	(495)
<b>DB2336DS</b>	10.56"	20.75" (268 to 527)	31 <sup>1</sup> / <sub>2</sub> "	(800)
<b>DB2936DS</b>	10.56"	26.75" (268 to 679)	31 <sup>1</sup> / <sub>2</sub> "	(800)
<b>DB4136DS</b>	10.56"	38.75" (268 to 984)	31 <sup>1</sup> / <sub>2</sub> "	(800)
<b>DB5336DS</b>	10.56"	50.75" (268 to 1289)	31 <sup>1</sup> / <sub>2</sub> "	(800)
<b>DB2348DS</b>	10.56"	20.75" (268 to 527)	43 <sup>1</sup> / <sub>2</sub> "	(1105)
<b>DB2948DS</b>	10.56"	26.75" (268 to 679)	43 <sup>1</sup> / <sub>2</sub> "	(1105)
<b>DB4148DS</b>	10.56"	38.75" (268 to 984)	43 <sup>1</sup> / <sub>2</sub> "	(1105)
<b>DB5348DS</b>	10.56"	50.75" (268 to 1289)	43 <sup>1</sup> / <sub>2</sub> "	(1105)

Part No.	Height (overall)		Width (overall)		Length (overall)		Wt./Each	
	In.	mm	In.	mm	In.	mm	lbs.	kg
<b>DB2318DS</b>	23"	(584)	25 <sup>5</sup> / <sub>8</sub> "	(651)	20.2"	(513)	33.31	(15.11)
<b>DB2918DS</b>	29"	(736)	25 <sup>5</sup> / <sub>8</sub> "	(651)	20.2"	(513)	35.00	(15.88)
<b>DB4118DS</b>	41"	(1041)	25 <sup>5</sup> / <sub>8</sub> "	(651)	20.2"	(513)	38.40	(17.42)
<b>DB5318DS</b>	53"	(1346)	25 <sup>5</sup> / <sub>8</sub> "	(651)	20.2"	(513)	41.80	(18.96)
<b>DB2324DS</b>	23"	(584)	31 <sup>5</sup> / <sub>8</sub> "	(803)	20.2"	(513)	34.15	(15.49)
<b>DB2924DS</b>	29"	(736)	31 <sup>5</sup> / <sub>8</sub> "	(803)	20.2"	(513)	35.84	(16.26)
<b>DB4124DS</b>	41"	(1041)	31 <sup>5</sup> / <sub>8</sub> "	(803)	20.2"	(513)	39.25	(17.80)
<b>DB5324DS</b>	53"	(1346)	31 <sup>5</sup> / <sub>8</sub> "	(803)	20.2"	(513)	42.65	(19.34)
<b>DB2336DS</b>	23"	(584)	43 <sup>5</sup> / <sub>8</sub> "	(1108)	20.2"	(513)	35.84	(16.26)
<b>DB2936DS</b>	29"	(736)	43 <sup>5</sup> / <sub>8</sub> "	(1108)	20.2"	(513)	37.56	(17.03)
<b>DB4136DS</b>	41"	(1041)	43 <sup>5</sup> / <sub>8</sub> "	(1108)	20.2"	(513)	40.95	(18.57)
<b>DB5336DS</b>	53"	(1346)	43 <sup>5</sup> / <sub>8</sub> "	(1108)	20.2"	(513)	44.34	(20.11)
<b>DB2348DS</b>	23"	(584)	55 <sup>5</sup> / <sub>8</sub> "	(1415)	20.2"	(513)	37.55	(17.03)
<b>DB2948DS</b>	29"	(736)	55 <sup>5</sup> / <sub>8</sub> "	(1415)	20.2"	(513)	39.25	(17.80)
<b>DB4148DS</b>	41"	(1041)	55 <sup>5</sup> / <sub>8</sub> "	(1415)	20.2"	(513)	42.65	(19.34)
<b>DB5348DS</b>	53"	(1346)	55 <sup>5</sup> / <sub>8</sub> "	(1415)	20.2"	(513)	46.03	(20.88)

A = Adjustable height from bottom of DURA-BLOK to top of horizontal channel.  
 B = Space between fittings that support horizontal channel.  
 Height (overall) = Distance from bottom of DURA-BLOK to top of upright channel.  
 Width (overall) = Distance from outside-to-outside of DURA-BLOK supports.  
 Length (overall) = Distance from end-to-end of DURA-BLOK supports.

Reference page 196 for general fitting and standard finish specifications.