

## Rack Mounted Horizontal Transition Trays For Patchcords and Jumpers

- Transition trays offer top and bottom field adjustable horizontal cable management support
- Bend radius is 1½" (38mm)
- Available for 19" (482mm) and 23" (584mm) racks
- Material: Aluminum
- Finish \_\_\_: Flat black powder coat (FB)  
Silver powder coat (SL)

Part Number	Depth		Width		Weight	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
<b>Top Transition Tray - 1½" (38mm) High</b>						
SB81319TT3__	3½"	(89)	19"	(482)	3.0	(1.36)
SB81319TT6__	6"	(152)	19"	(482)	4.0	(1.81)
SB81323TT3__	3½"	(89)	23"	(584)	4.0	(1.81)
SB81323TT6__	6"	(152)	23"	(584)	5.0	(2.27)
<b>Upper Transition Tray</b>						
SB81319UT3__	3½"	(92)	19"	(482)	3.0	(1.36)
SB81319UT6__	6"	(152)	19"	(482)	4.0	(1.81)
SB81323UT3__	3½"	(92)	23"	(584)	4.0	(1.81)
SB81323UT6__	6"	(152)	23"	(584)	5.0	(2.27)
<b>Lower Transition Tray</b>						
SB81319LT3__	3½"	(92)	19"	(482)	4.0	(1.81)
SB81319LT6__	6"	(152)	19"	(482)	5.0	(2.27)
SB81323LT3__	3½"	(92)	23"	(584)	5.0	(2.27)
SB81323LT6__	6"	(152)	23"	(584)	6.0	(2.72)
<b>Lower Transition Tray - Double - 3½" (89mm) High</b>						
SB81319LTD3__	3½"	(92)	19"	(482)	4.0	(1.81)
SB81319LTD6__	6"	(152)	19"	(482)	5.0	(2.27)
SB81323LTD3__	3½"	(92)	23"	(584)	5.0	(2.27)
SB81323LTD6__	6"	(152)	23"	(584)	6.0	(2.72)
<b>Transition Tray - 1⅞" (47mm) High</b>						
SB813TP3__	3¼"	(82)	15.8"	(401)	2.0	(0.91)
SB813TP6__	5¾"	(146)	15.8"	(401)	4.0	(1.81)

Specify part number and finish when ordering.

