

## RCM+ Rack Mounted Vertical Cable Manager With Cover cont. Double Sided High Density Plastic Finger Style

Part Number	Fits Rack Height of In. (mm)	'A' In. (mm)	'B' In. (mm)	'C' In. (mm)	Weight Each Lbs. (kg)	Max CAT6A Cables (0.375" OD) (50% Fill)
3 <sup>5</sup> / <sub>8</sub> " (92mm) Wide x 21 <sup>5</sup> / <sub>8</sub> " (549mm) Deep						
SB86083D066__	66" (1676)	60 <sup>3</sup> / <sub>8</sub> " (1533)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	23.7 (10.7)	218
SB86083D072__	72" (1829)	67 <sup>3</sup> / <sub>8</sub> " (1711)	2" (50.8)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	26.5 (12.0)	218
SB86083D078__	78" (1981)	72 <sup>5</sup> / <sub>8</sub> " (1845)	2 <sup>3</sup> / <sub>4</sub> " (69.9)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	28.5 (12.9)	218
SB86083D084__	84" (2133)	79 <sup>5</sup> / <sub>8</sub> " (2022)	1 <sup>3</sup> / <sub>4</sub> " (44.4)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	30.9 (14.0)	218
SB86083D090__	90" (2286)	84 <sup>7</sup> / <sub>8</sub> " (2156)	2 <sup>1</sup> / <sub>2</sub> " (63.5)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	33.1 (15.0)	218
SB86083D096__	96" (2438)	90 <sup>1</sup> / <sub>8</sub> " (2289)	3 <sup>1</sup> / <sub>4</sub> " (82.6)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	35.3 (16.0)	218
SB86083D108__	108" (2743)	102 <sup>3</sup> / <sub>8</sub> " (2600)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	39.9 (18.1)	218
6" (152mm) Wide x 21 <sup>5</sup> / <sub>8</sub> " (549mm) Deep						
SB86086D066__	66" (1676)	60 <sup>3</sup> / <sub>8</sub> " (1533)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	26.7 (12.1)	421
SB86086D072__	72" (1829)	67 <sup>3</sup> / <sub>8</sub> " (1711)	2" (50.8)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	29.9 (13.6)	421
SB86086D078__	78" (1981)	72 <sup>5</sup> / <sub>8</sub> " (1845)	2 <sup>3</sup> / <sub>4</sub> " (69.9)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	32.1 (14.6)	421
SB86086D084__	84" (2133)	79 <sup>5</sup> / <sub>8</sub> " (2022)	1 <sup>3</sup> / <sub>4</sub> " (44.4)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	34.9 (15.8)	421
SB86086D090__	90" (2286)	84 <sup>7</sup> / <sub>8</sub> " (2156)	2 <sup>1</sup> / <sub>2</sub> " (63.5)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	37.2 (16.9)	421
SB86086D096__	96" (2438)	90 <sup>1</sup> / <sub>8</sub> " (2289)	3 <sup>1</sup> / <sub>4</sub> " (82.6)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	39.9 (18.1)	421
SB86086D108__	108" (2743)	102 <sup>3</sup> / <sub>8</sub> " (2600)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	45.0 (20.4)	421
10" (254mm) Wide x 21 <sup>5</sup> / <sub>8</sub> " (549mm) Deep						
SB860810D066__	66" (1676)	60 <sup>3</sup> / <sub>8</sub> " (1533)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	38.4 (17.4)	757
SB860810D072__	72" (1829)	67 <sup>3</sup> / <sub>8</sub> " (1711)	2" (50.8)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	42.8 (19.4)	757
SB860810D078__	78" (1981)	72 <sup>5</sup> / <sub>8</sub> " (1845)	2 <sup>3</sup> / <sub>4</sub> " (69.9)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	46.1 (20.9)	757
SB860810D084__	84" (2133)	79 <sup>5</sup> / <sub>8</sub> " (2022)	1 <sup>3</sup> / <sub>4</sub> " (44.4)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	49.9 (22.6)	757
SB860810D090__	90" (2286)	84 <sup>7</sup> / <sub>8</sub> " (2156)	2 <sup>1</sup> / <sub>2</sub> " (63.5)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	52.6 (23.9)	757
SB860810D096__	96" (2438)	90 <sup>1</sup> / <sub>8</sub> " (2289)	3 <sup>1</sup> / <sub>4</sub> " (82.6)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	56.8 (25.8)	757
SB860810D108__	108" (2743)	102 <sup>3</sup> / <sub>8</sub> " (2600)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	64.0 (29.1)	757
12" (305mm) Wide x 21 <sup>5</sup> / <sub>8</sub> " (549mm) Deep						
SB860812D066__	66" (1676)	60 <sup>3</sup> / <sub>8</sub> " (1533)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	46.3 (21.0)	926
SB860812D072__	72" (1829)	67 <sup>3</sup> / <sub>8</sub> " (1711)	2" (50.8)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	51.4 (23.3)	926
SB860812D078__	78" (1981)	72 <sup>5</sup> / <sub>8</sub> " (1845)	2 <sup>3</sup> / <sub>4</sub> " (69.9)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	55.4 (25.1)	926
SB860812D084__	84" (2133)	79 <sup>5</sup> / <sub>8</sub> " (2022)	1 <sup>3</sup> / <sub>4</sub> " (44.4)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	60.0 (27.2)	926
SB860812D090__	90" (2286)	84 <sup>7</sup> / <sub>8</sub> " (2156)	2 <sup>1</sup> / <sub>2</sub> " (63.5)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	63.6 (28.9)	926
SB860812D096__	96" (2438)	90 <sup>1</sup> / <sub>8</sub> " (2289)	3 <sup>1</sup> / <sub>4</sub> " (82.6)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	68.7 (31.2)	926
SB860812D108__	108" (2743)	102 <sup>3</sup> / <sub>8</sub> " (2600)	3" (76.2)	2 <sup>5</sup> / <sub>8</sub> " (66.7)	77.1 (35.0)	926

Specify part number and finish when ordering.

A = Height of RCM+ vertical section without doors

B = Distance between the top of the rack and the top of the RCM+ cable manager

C = Distance between the floor and the lowest part of the RCM+ cable manager