

MOUNTING & ROLLER BRACKETS

| PART NO. | REEL SERIES | | | | | | | | | |
|---|----------------------------|-------------|---|---|----|----|-----------|------|------------|------------|
| | P | SH, MP & HP | T | C | EN | PC | P-W & SHW | P-WC | Alumi-Pro® | Nitro-Pro® |
|  <p>Swing Bracket For vertical surface mounting, allows reel to swing 180°. Powder coated crinkle black 3/16" steel. Weight: 5 lbs.</p> | 15720 | • | • | | | • | • | • | • | • |
| | 15725 | | | • | • | | | | | |
|  <p>Swivel Bracket For horizontal surface mounting, ball bearing rotation, allows reel to swivel 345°. Powder coated crinkle black heavy gauge steel. Weight: 6 lbs. NOT FOR USE IN CEILING APPLICATIONS.</p> | 15721 | • | • | • | • | • | • | • | • | • |
| | | | | | | | | | | |
|  <p>EZ-Up Bracket Reel easily slides in & out for easy overhead mounting. Use as an alternative to the #MR-1. Must be ordered with #15724 for "I" or "H" beam installations. Weight: 6.5 lbs.</p> | 15723 | • | • | • | • | • | • | • | • | • |
| | | | | | | | | | | |
|  <p>EZ-Up "I" or "H" Beam Adapter Must be ordered with #15723. Powder coated crinkle black, all steel construction. Weight: 5 lbs.</p> | 15724 | • | • | • | • | • | • | • | • | • |
| | | | | | | | | | | |
|  <p>Mounting Bracket For overhead mounting, fits 3" to 8 1/2" flange on "I" or "H" beam. Powder coated crinkle black 3/16" bent steel. Weight: 13 lbs.</p> | MR-1 | • | • | | | • | • | • | • | • |
| | MRT-1 | | | • | • | | | | | |
|  <p>4-Way Roller Bracket Heavy gauge steel, powder coated Coxreels blue (4RB) Available in stainless steel (4RB-SS). Weight: 1 lbs.</p> | 4RB 1/4"-3/4" | • | • | • | • | • | • | • | • | • |
| | 4RB-SS 1/4"-3/4" | • | • | • | • | • | • | • | • | • |

S SERIES MOUNTING & ROLLER BRACKETS

| PART NO. | S SERIES MODELS | | | |
|--|-----------------|-------------|-------------|-------------|
| | SR13 & SL13 | SR15 & SL15 | SR17 & SL17 | SR19 & SL19 |
|  <p>Dual Side Mount Bracket Heavy gauge steel, powder coated crinkle black. Weight: 5 lbs.</p> | 15726-13 | • | | |
| | 15726-15 | | • | |
| | 15726-17 | | | • |
| | 15726-19 | | | |
|  <p>Single Side Mount Bracket Heavy gauge steel, powder coated crinkle black. Weight: 2 lbs.</p> | SMB1 | • | • | |
| | SMB2 | | | • |
| | SMB3 | | | |

PVC INLET HOSE ASSEMBLIES

| PART NO. | FITTINGS | I.D. | LENGTH | PSI |
|-----------------|--|-----------|--------|------|
| 5150-1.5 | 1/4" Male x Female NPT | 1/4" | 18" | 300 |
| 5153-1.5 | 3/8" Male x Female NPT | 3/8" | 18" | 300 |
| 5154-1.5 | 1/2" Male x Female NPT | 1/2" | 18" | 300 |
| 5155-1.5 | 3/4" Male x Male NPT | 3/4" | 18" | 300 |
| 5224-1.5 | 3/8" Male x Male NPT | 3/8" | 18" | 3000 |
| 5256-1.5 | 1/2" Male x Male NPT | 1/2" | 18" | 2500 |
| 5290-1.5 | 3/4" Male x Male NPT | 3/4" | 18" | 1500 |
| 5304-1.5 | 1/4" Male x Male NPT | 1/4" | 18" | 5000 |
| 5336-1.5 | 3/8" Male x Male NPT | 3/8" | 18" | 4000 |
| 15717 | Garden 3/4" NPTM (w/Part #10781) x 3/4" NP | 3/4" | 48" | 300 |
| 5423-1.5 | Twin Grade R 1/8" NPTM x BB 9-16 UNF | 1/4" Twin | 18" | 200 |
| 5424-1.5 | "T" Grade Twin Grade R 1/8" NPTM x BB 9-16 UNF | 1/4" Twin | 18" | 200 |

90° ELBOWS

| PART NO. | FITTING THREAD | I.D. | PSI |
|--------------|----------------------------|------|------|
| 6088 | Brass LP Male x Female NPT | 1/4" | 300 |
| 208 | Brass LP Male x Female NPT | 3/8" | 300 |
| 222 | Brass LP Male x Female NPT | 1/2" | 300 |
| 385 | Brass LP Male x Female NPT | 3/4" | 300 |
| 500 | Steel MP Male x Female NPT | 3/8" | 3000 |
| 1671 | Steel MP Male x Female NPT | 1/2" | 3000 |
| 15014 | Steel MP Male x Female NPT | 3/4" | 1250 |
| 616 | Steel HP Male x Female NPT | 1/4" | 5000 |
| 617 | Steel HP Male x Female NPT | 3/8" | 5000 |

HOSE STOPS & GUARDS

| HOSE STOPS PART NO. | HOSE GUARD PART NO. | HOSE | | OVERALL |
|---------------------|---------------------|----------------|----------|---------|
| | | I.D. | O.D. | |
| 131 | 237-1 | 1/4" | 1/2" | 2 1/2" |
| 633 | 237-1 | 1/4" Twin Line | | 3 1/2" |
| 131-3 | 237-1 | 3/8" | 2 1/32" | 2 1/2" |
| 131-4 | 398-1 | 1/2" | 3/4" | 2 1/2" |
| 254 | - | 1/2" | 3/4" | 3 1/2" |
| 430 | 398-1 | 3/4" | 1" | 3 1/2" |
| 20214 | - | 1" | 19/16" | 5" |
| 20215 | - | 1 1/4" | 1 13/16" | 5" |
| 20216 | - | 1 1/2" | 2 1/16" | 5" |
| 20217 | - | 2" | 2 9/16" | 5" |

BEND RESTRICTORS

| ADD SUFFIX | I.D. | DESCRIPTION | PSI |
|-------------|------|---------------------------|-----|
| -BXB | 1/4" | Black PVC Bend Restrictor | |
| -BXB | 3/8" | Black PVC Bend Restrictor | |
| -BXB | 1/2" | Black PVC Bend Restrictor | |

Designed to limit the degree of bending without compromising the integrity of the hose assembly while also preventing the hose-end from kinking, excessive wearing, and tearing.

QUICK DISCONNECTS

| PART NO. | I.D. | DESCRIPTION | CONNECTION | PSI |
|----------------|------|-------------------|------------|-----|
| 10759-1 | 1/4" | Quick" Disconnect | NPT (F) | 300 |
| 10759-2 | 3/8" | Quick Disconnect | NPT (F) | 300 |

Quick disconnect couplings thread onto end of hose fitting to provide fast, leak-proof connections for low pressure hose lines. Conveniently connect, interchange, and secure pneumatic tools or other spraying devices to any air, water, chemical or other hose lines.

SPRING DRIVEN

MOTORIZED

HAND CRANK

