

Series 2000 Power Return Tapes



2125

- Case designed to fit perfectly in the hand
- Lightweight, high strength chrome finished case
- Fits easily into most tape holsters
- Bright yellow blade has clear easy-to-read numerals
- Toggle lock is positioned for convenient operation and holds the blade securely in any position
- Virtually unbreakable Quad Hook[®]; four rivets for extra strength (1" blade only)
- Cushioned blade return
- Removable belt clip
- All shelf pack power tapes on this page are carded

Cat. No.	UPC No.	Blade Size		Blade Style	Pack Wt.		Shelf Pack	Replacement Blade	UPC No.
		Width	Length		lb	kg			
2133	037103108580	1"	33'	A5	8.00	3.63	6	-	-
2133D	037103108524	1"	33' Engineer's	A4	8.00	3.63	6	-	-
2410CME	037103108517	1"(25mm)	33'(10m)	A30	8.00	3.63	6	-	-
2130	037103442130	1"	30'	A5	6.65	3.02	6	RY430	037103459862
2049CME	037103442901	1"(25mm)	30'(9m)	A30	6.65	3.02	6	-	-
2125	037103441539	1"	25'	A5	5.68	2.58	6	RY425	037103457042
2048CME	037103441829	1"(25mm)	26'(8m)	A30	5.68	2.58	6	-	-
2325	037103442123	3/4"	25'	A2	4.56	2.07	6	RY325	037103452351
2325D	037103013316	3/4"	25' Engineer's	A4	4.56	2.07	6	-	-
2338CME	037103013255	3/4"(19mm)	26'(8m)	A13	4.56	2.07	6	-	-
2316	037103441737	3/4"	16'	A2	3.14	1.42	6	RW316	037103452337
2335ME	037103013293	3/4"(19mm)	16'(5m)	A12	3.14	1.42	6	-	-
2035CM	037103057532	19mm	5m	A9	3.14	1.42	6	-	-
2035CME	037103441997	3/4"(19mm)	16'(5m)	A13	3.14	1.42	6	RY35CME	037103461018
2312	037103441720	3/4"	12'	A2	2.4	1.07	6	-	-
2312D	037103013309	3/4"	12' Engineer's	A4	2.4	1.07	6	RW312	037103452207
2034CME	037103003546	3/4"(19mm)	13'(4m)	A13	2.6	1.18	6	-	-
2033CME	037103104007	3/4"(19mm)	10'(3m)	A13	2.38	1.08	6	-	-
2333ME	037103013286	3/4"(19mm)	10'(3m)	A12	2.2	1.0	6	-	-
2212	037103013231	1/2"	12'	A1	1.9	0.85	6	RY212	037103450388
2212X	037103013477	1/2"	12' Engineer's	A7	1.9	0.85	6	-	-
2212DX	037103124920	1/2"	12' Engineer's	A31	1.9	0.85	6	-	-
2024CME	037103103994	1/2"(13mm)	13'(4m)	A13	2.0	0.90	6	-	-
2210	037103013323	1/2"	10'	A1	1.8	0.80	6	RY210	037103450234
2210MEX	037103097897	1/2"(13mm)	10'(3m) Engineer's	A36	1.8	0.80	6	-	-
2223CME	037103013224	1/2"(13mm)	10'(3m)	A13	1.8	0.80	6	-	-