

ATLAS® CHROME CLAD®

- Heavy-duty frame designed for years of rugged use
- All frames include a grounding strap
- Blade counts graduated feet down to 1/8th inches, for instantaneous foot readings
- Plumb bob must be ordered separately



| Cat. No. | Bob Cut | Blade Width | Blade Length | Blade Style | Product Weight |
|---------------|---------|---------------|--------------|-------------|----------------|
| C129012SFN | 590 | 1/2 in | 18 ft | D4 | 1.60 lb |
| C1290SF590N | 590 | 1/2 in | 25 ft | D4 | 1.80 lb |
| C1291SF590N | 590 | 1/2 in | 33 ft | D4 | 1.90 lb |
| C1293SF590N | 590 | 1/2 in | 50 ft | D4 | 2.30 lb |
| C2910MME590N | 590GM | 13 mm, 1/2 in | 10 m, 33 ft | D6 | 1.95 lb |
| C2915MME590N | 590GM | 13 mm, 1/2 in | 15 m, 50 ft | D6 | 2.35 lb |
| C2920MME150MN | 150 mm | 13 mm, 1/2 in | 20 m, 66 ft | D6 | 2.50 lb |
| C2920MME590N | 590GM | 13 mm, 1/2 in | 20 m, 66 ft | D6 | 2.70 lb |
| C2930MME590N | 590GME | 13 mm, 1/2 in | 30 m, 98 ft | D6 | 3.95 lb |

ATLAS® CHROME CLAD®/NUBIAN® DOUBLE DUTY

- Heavy-duty frame designed for years of rugged use
- All frames include a grounding strap
- Plumb bob must be ordered separately



| Cat. No. | Bob Cut | Blade Width | Blade Length | Blade Style | Product Weight |
|---------------|---------|---------------|--------------|-------------|----------------|
| CN129012SF5N | 590 | 1/2 in | 18 ft | D1 | 1.60 lb |
| CN1290SF590N | 590 | 1/2 in | 25 ft | D1 | 1.60 lb |
| CN1291SF590N | 590 | 1/2 in | 33 ft | D1 | 1.90 lb |
| CN1293SDF590N | 590 | 1/2 in | 50 ft | D2 | 2.20 lb |
| CN1293SF5871N | 5871/2 | 1/2 in | 50 ft | D1 | 2.30 lb |
| CN1293SF590N | 590 | 1/2 in | 50 ft | D1 | 2.20 lb |
| CN1294SF5871N | 5871/2 | 1/2 in | 66 ft | D1 | 2.70 lb |
| CN1294SF590N | 590 | 1/2 in | 66 ft | D1 | 2.60 lb |
| CN1295SF590N | 590 | 1/2 in | 75 ft | D1 | 2.90 lb |
| CN1296SF590N | 590 | 1/2 in | 100 ft | D1 | 3.56 lb |
| CN1290SMEN | 590 | 13 mm, 1/2 in | 8 m, 26 ft | D3 | 1.80 lb |
| CN1293SMEF59N | 590 | 13 mm, 1/2 in | 15 m, 50 ft | D3 | 2.30 lb |
| CN1294SMEF59N | 590 | 13 mm, 1/2 in | 20 m, 66 ft | D3 | 2.60 lb |
| CN1295SME590N | 590 | 13 mm, 1/2 in | 23 m, 75 ft | D3 | 2.88 lb |
| CN1295SMEN | 5871/2 | 13 mm, 1/2 in | 23 m, 75 ft | D3 | 2.70 lb |
| CN1296SMEF59N | 590 | 13 mm, 1/2 in | 30 m, 100 ft | D3 | 3.980 lb |
| CN1298SME590N | 590 | 13 mm, 1/2 in | 38 m, 125 ft | D3 | 4.20 lb |