

PHV SERIES TAPE MEASURES

- Ergonomic case design for better fit in-hand during measuring
- Overmold case protects the tape from impact and makes it easier to grip
- Toggle lock positioned on top of the tape doesn't require sliding to lock
- Reinforced quad-rivet end hook prevents end hook from ripping off of blade



Cat. No.	Blade Width	Blade Length	Blade Style	Magnetic	Product Weight
PHV1023CMEN	13 mm, 1/2 in	3 m, 10 ft	A20	No	0.29 lb
PHV1023CMN	13 mm, 1/2 in	3 m, 10 ft	A9	No	0.29 lb
PHV1034DMN	19 mm, 3/4 in	3.7 m, 12 ft	A19	No	0.60 lb
PHV1035CMEN	19 mm, 3/4 in	5 m, 16 ft	A20	No	0.62 lb
PHV1035CMN	19 mm, 3/4 in	5 m, 16 ft	A9	No	0.62 lb
PHV1048CMEN	25 mm, 1 in	8 m, 26 ft	A20	No	1.07 lb
PHV1048CMN	25 mm, 1 in	8 m, 26 ft	A9	No	1.07 lb
PHV1312DN	3/4 in	12 ft	A4	No	0.60 lb
PHV1312N	3/4 in	12 ft	A2	No	0.60 lb
PHV1316N	3/4 in	16 ft	A2	No	0.62 lb
PHV1410CMEN	25 mm, 1 in	10 m, 33 ft	A20	No	1.34 lb
PHV1425DN	1 in	25 ft	A4	No	1.07 lb
PHV1425N	1 in	25 ft	A5	No	1.07 lb
PHV1433N	1 in	33 ft	A5	No	1.34 lb

P SERIES TAPE MEASURES

- Ergonomic case design for better fit in-hand during measuring
- Toggle lock positioned on top of the tape doesn't require sliding to lock
- Multi-riveted end hook for added durability
- Compact chrome-finished case



Cat. No.	Blade Width	Blade Length	Blade Style	Magnetic	Product Weight
P2212XN	1/2 in	12 ft	A7	No	0.32 lb
P2210MEXN	13 mm, 1/2 in	3 m, 10 ft	A22	No	0.29 lb
P2133DN	1 in	33 ft	A4	No	1.72 lb