

Built Better in Every Way

Here are a few reasons why Dandy Lifts are the world's best lifter/transporters:

- Durable enamel paint and chrome finish
- Steerable caster-type wheels
- Multi-Grip position, contoured handle
- Qwik-Grip lowering handle
- 180° access foot pump pedal
- Foot activated parking lock
- Infinite height adjustment within range
- 20:1 mechanical advantage hydraulics

The Widest Line of Models and Configurations



Light Duty - Dandy L-150



Medium Duty - Dandy A-500



Heavy Duty - Dandy A-800



Medium Duty/High Lift
Dandy A-350W



Auto Leveling - Dandy Leveler
Dandy DLV-150 / Dandy DLV-500



Pallet/Skid Lifter Transporter
Dandy M-500L

Dandy Lifts & Dandy Levelers

Dandy Model	Maximum Capacity	Overall Dim. (W x L)	Handle Height	Platform Size (W x L)	Low Height	Vertical Travel	Raised Height	Weight
L-150	330 lbs	17.7" x 37.7"	36.0"	17.7" x 28"	8.3"	20.7"	29"	82 lbs
L-250	550 lbs	19.7" x 38.2"	36.2"	19.7" x 31.5"	9.5"	22.2"	31.8"	115 lbs
A-500	1,100 lbs	23.6" x 42.1"	37.8"	23.6" x 35.8"	11.8"	24.8"	36.6"	194 lbs
A-800	1,760 lbs	23.6" x 45.9"	38.8"	23.6" x 39.4"	13"	27.2"	40.2"	275 lbs
A-350W	770 lbs	23.6" x 42.1"	37.8"	23.6" x 35.8"	13.6"	36.2"	49.8"	229 lbs
Leveler DLV-150	330 lbs	17.1" x 32.6"	36.0"	17.7" x 36.2"	10.8"	15.3"	26.2"	100 lbs
Leveler DLV-500	1,100 lbs	23.6" x 42.1"	37.4"	23.6" x 35.8"	15"	16.5"	31.5"	210 lbs
M-500L	1,100 lbs	19.7" x 55.4"	37.1"	19.7" x 37.1"	3.2"	26.3"	29.5"	174 lbs