



**For indoor and outdoor installations**

**Connecting plate with high short-circuit carrying capacity**

**Allows for single-pole connection of the short-circuiting cables**

**For fixed ball points Ø20, Ø25 mm or grooved ring bolt Ø16 mm**

**EAP 3 KFP 20 KKH**

<b>Diameter of the fixed point</b>	20 mm
<b>Max. short-circuit current / 0.5 s</b>	33.5 kA
<b>Cable cross section</b>	120 mm <sup>2</sup>
<b>Max. short-circuit current I<sub>k</sub> / 1 s</b>	23.7 kA

<b>Fixed point</b>	Brass (CuNi2Si) / gal Sn
<b>Threaded bolt</b>	StSt A2-70
<b>Hexagon nut</b>	DIN 985-M12-8 / gal Zn; DIN 985-M16-8 / gal Zn

**Ordering information**

<b>Type</b>	EAP 3 KFP 20 KKH
<b>Part No.</b>	<b>728 300</b>
<b>Packing unit</b>	1 pc

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.