

## EKV K 50 8500 (751 086)



Figure without obligation

Phase cable end: Earth clamp for overhead contact lines, clamping range Ø4–15 mm (Part No. 784 755)

Earth cable end: Clamp for railway tracks with tommy bar (Part No. 792 450)

Type	EKV K 50 8500
Part No.	751 086
Material (cable)	Cu
Version	Single-pole
Cable cross-section (phase side)	50 mm <sup>2</sup>
Cable cross-section (earth side)	50 mm <sup>2</sup>
Length of single-pole cable	8500 mm
Fully insulated	No
Standard	EN/IEC 61230 (DIN VDE 0683-100) and IEC 61138
Max. short-circuit current I <sub>k</sub> 0.06 s	34.0 kA
DB drawing No.	3 Ebgw 01.51/67
Weight	8,99 kg
Customs tariff number (Comb. Nomenclature EU)	85359000
GTIN	4013364126626
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.