

PAV 3+1 16 ZAK (758 099)



Figure without obligation

Type	PAV 3+1 16 ZAK
Part No.	758 099
Cable length (A / B / C)	1750 mm
Cable length (D)	3200 mm
Cable cross-section	16 mm ²
Cable sheath	transparent
Clamping range	5-25 mm
Colour (clamp A / B / C)	black
Colour (clamp D)	red
Possible clamp operations	> 500
Max. continuous operating current	10 A
Operating temperature range	-30 °C ... +50 °C
Storage temperature range	-40 °C ... +70 °C
Cable structure	bare fine-stranded Cu wire according to VDE 0295-6
Dielectric strength (cable sheath)	min. 10 kV/mm
Wall thickness (insulation)	1.20 mm (typical)
Insulation	PVC compound TM2 according to HD21.1
Weight	3,06 kg
Customs tariff number (Comb. Nomenclature EU)	85369095
GTIN	4013364287587
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.