



Insulating rod with M55 adapter / gear coupling for attaching PHE III electronic indicator.

Not for use in wet weather

For use in indoor and outdoor installations

Threaded coupling with protection against twisting and bridging

Modular system for a variety of applications

For use as switching rod, earthing rod, operating rod and/or insulating rod

SSK M55 500	
Diameter	65 / 30 mm
Total length	560 mm
Position	1
Top section of switching rod	Glass-fibre-reinforced polyester tube, Ø30 mm, grey, switching pin St, sheathed overall in PVC
Adapter	Plastic universal gear coupling, yellow
Operating head	Plastic coupling (long T pin shaft), yellow; Aluminium coupling (T pin shaft)
Insulating tube	Glass-fibre-reinforced polyester tube, Ø43 mm, grey or yellow
Coupling	Plastic threaded coupling M55x4 with protection against twisting, with cap nut Ø65 mm, black
Ordering information	
Type	SSK M55 500
Part No.	766 064
Packing unit	1 pc

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.