

EKS TI KVS SBK (766 302)

- Partly insulated (TI), shock-proof version
- Fully equipped kit for cable distribution cabinets
- Other cable lengths can be selected online via the earthing and short-circuiting configurator



Figure without obligation

Figure without obligation

Kit includes:

Pos.	Part No.	Pos.	Part No.
1	1x 766 300	6	3x 745 018
3	1x VSUN6NV	9	1x 745 400

For more detailed information on these products, see Accessories chapter.

Type	EKS TI KVS SBK
Part No.	766 302
Variant No. of EaS device	VSUN6NV
Dimensions	380 x 260 x 80 mm
Standard	EN/IEC 61230 (DIN VDE 0683-100)
Temperature range	-25 °C ... +55 °C
Weight	4,38 kg
Customs tariff number (Comb. Nomenclature EU)	85369095
GTIN	4013364051317
PU	1 pc(s)

Attention: Please state the relevant Variant No. when ordering.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.