



SPN 500B (766 660)



Figure without obligation

Type	SPN 500B
Part No.	766 660
Nominal voltage range (U _N)	50 ... 500 V
Frequency range	15 ... 500 Hz and DC
Dimensions (indicator)	274 x 75 x 47 mm
Standard	EN/IEC 61243-3 (DIN VDE 0682-401)
Temperature range	-15 °C ... +45 °C
Material (indicator)	Safety enclosure made of solid rubber
Indicator	Direct-reading instrument, LCD and LED
Connecting cable	PUR-sheathed cable, highly flexible, 1000 mm
Overvoltage category	CAT IV 500 V
Type	Two-pole
Battery	Lithium
For	Indoor and outdoor installations
Degree of protection	IP 65
For use at	
Weight	460 g
Customs tariff number (Comb. Nomenclature EU)	90303370
GTIN	4013364302464
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.