

PHE3 10 30 S (767 731)

- Easy transport due to detachable insulating stick (M12) and test prod
- Insulating stick with plug-in coupling for extending the handle



Figure without obligation




Figure without obligation

Type	PHE3 10 30 S
Part No.	767 731
Nominal voltage (U _N)	10 ... 30 kV
Type of voltage	a.c.
Frequency	50 Hz
Category	S 64
Total length (l _c)	1675 mm
Insertion depth (l _o)	880 mm
Length (indicator with test prod)	1050 mm
Standard	EN/IEC 61243-1 (DIN VDE 0682-411)
Temperature range	-25 °C ... +55 °C, climatic category N
Design	Complete
For use at	☝
For	Indoor and outdoor installations
Application	Switchgear installations and overhead lines
Design	Single-pole
Indication	Acoustic and visual
Self-testing element	Yes
Material (test electrode)	Copper alloy/gal Sn
Material (test prod)	Glass-fibre reinforced epoxy resin tube
Material (indicator)	Plastic, fully insulated
Material (insulating stick)	Glass-fibre reinforced polyester tube
Weight	1,29 kg
Customs tariff number (Comb. Nomenclature EU)	90303370
GTIN	4013364070875
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.