

## PSK 4 30 SQL (784 201)

- Earthing and short-circuiting devices can be configured online via the earthing and short-circuiting configurator
- For connecting the phase cables of single-pole and three-pole earthing and short-circuiting devices to the overhead line
- PK1 anti-rotation protection and long threaded T pin shaft



Figure without obligation




Figure without obligation

Type	PSK 4 30 SQL
Part No.	784 201
Clamping range Ø	4 ... 30 mm
Anti-rotation protection	PK1
For cable cross-section Cu	16 ... 70 mm <sup>2</sup>
Max. short-circuit current I <sub>k</sub> 0.5 s	19.5 kA
Max. short-circuit current I <sub>k</sub> 1 s	13.8 kA
Standard	EN/IEC 61230 (DIN VDE 0683-100), threaded T pin shaft DIN 48087
Temperature range	-25 °C ... +55 °C
Material (pressure plate)	Aluminium alloy
Material (clamp body)	Aluminium alloy
Material (shaft)	Copper alloy/gal Sn
Weight	880 g
Customs tariff number (Comb. Nomenclature EU)	85359000
GTIN	4013364006591
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

**The clamps must be designed for the same maximum short-circuit current as the earthing and short-circuiting cables!**