

IMG SAN 1M 10M (785 459)

- Not permitted as standing surface insulation for live working.



Figure without obligation

Type	IMG SAN 1M 10M
Part No.	785 459
Nominal voltage up to (U_N)	50 kV
Material	Polymer NR/SBR
Temperature resistance	-55 °C ... +70 °C
Length	10 m
Width	1000 mm
Thickness	4.5 mm
Colour	Grey *
Standard	VDE 0303-21
Weight	56 kg
Customs tariff number (Comb. Nomenclature EU)	40082110
GTIN	4013364115057
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.