

ES YM2 16 (716 001)



Figure without obligation

The cable is delivered without crimped cable lugs and can be ordered by the metre.

Type	ES YM2 16
Part No.	716 001
Version	Single-pole
Cable cross-section	16 mm ²
Minimum order quantity ¹⁾	1 m
Standard	EN/IEC 61138 (DIN VDE 0283-3) and EN/IEC 61230 (DIN VDE 0683-100)
Temperature range	-25 °C ... +55 °C
Material (cable)	E-Cu, extra finely stranded and highly flexible
Material (sheath)	Thermoplastic polymer (flexible PVC compound YM2)
Weight	1 m/pc(s)
Customs tariff number (Comb. Nomenclature EU)	85446010
GTIN	4013364010406
PU	1 pc(s)

¹⁾ Length of earthing cable to be specified when ordering (in whole metres).

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.