

## EKV1+0 35 VGHVBP5 (VGHVBP5)



Figure without obligation

Type	EKV1+0 35 VGHVBP5
Part No.	VGHVBP5
Version	Single-pole
Cable cross-section (phase side)	35 mm <sup>2</sup>
Cable cross-section (earth side)	35 mm <sup>2</sup>
Length of single-pole cable	5000 mm
Cable cross-section	35 mm <sup>2</sup>
Fully insulated	No
Max. short-circuit current I <sub>k</sub> 0.5 s	6.5 kA
Max. short-circuit current I <sub>k</sub> 1 s	4.6 kA
Crimped cable lug	PK1
Standard	EN/IEC 61138 (DIN VDE 0283-3) and EN/IEC 61230 (DIN VDE 0683-100)
Temperature range	-25 °C ... +55 °C
Material (cable)	Al
Material (sheath)	Thermoplastic polymer (flexible PVC compound YM2)
Hole (cable lug)	Ø12.5 mm
Weight	1,12 kg
Customs tariff number (Comb. Nomenclature EU)	85359000
GTIN	4013364360389
PU	1 pc(s)

**Attention:** Please state the relevant Variant No. when ordering.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.