

# 225 SERIES

## Horizontal Hold Down Clamps | Product Overview

### Features:

- Low profile
- Stainless steel model furnished without plastic grip
- Available with DESTACO® Toggle Lock Plus

### Applications:

- Assembly
- Checking fixtures
- Closures
- Woodworking

### Also Available:

See page MC-ACC-1 for accessories  
Accommodates M8 or 5/16" spindle accessory

Covered under one or more U.S./International Patents

**225-U**  
Flanged Base  
U-Bar



**225-USS**  
Flanged Base, U-Bar,  
Stainless Steel



**225-UR**  
Flanged Base, U-Bar  
with DESTACO®  
Toggle Lock  
Plus



**225-UB** ⓘ  
Straight Base  
U Bar



**225-UBSS** ⓘ  
Straight Base, U Bar,  
Stainless Steel



## Technical Information

Model	Max. Holding Capacity	Clamp Bar Opening (+10°)	Handle Opening (+10°)	Weight	Accessories (Supplied)	
					Spindle Assembly	Flanged Washers
225-U	2220 N [500 lbf]	92°	70°	0,25kg [0.55lb]	225208-M	507107
225-USS	2670 N [600 lbf]				207943-M	507907
225-UR	2220 N [500 lbf]			0,31kg [0.69lb]	225208-M	507107
225-UB ⓘ					0,25kg [0.55lb]	207943-M
225-UBSS ⓘ	2670 N [600 lbf]					

ⓘ This item is available upon request