

10.8V LI-ION CROSS LINE LASER (GREEN BEAM)

10.8V XR

DCE088D1G

Beam Colour	Green
Accuracy	+/-3 mm @ 10m
Self-Levelling Range	+/-4°
Max. Working Range with Detector	30-50m
IP Rating	65
Number of Beams	2 - Horizontal, Vertical
Tripod Connection	1/4" x 5/8"
Pendulum Lock	Yes
Laser Class	2
Modes	Vertical Only, Horizontal Only, Cross Line



ALSO AVAILABLE AS:

DCE088NR



CROSS LINE LASER (RED BEAM)

DW088K

Beam Colour	Red
Accuracy	+/-3 mm @ 10m
Self-Levelling Range	+/-4°
Max. Working Range	15-50m
IP Rating	54
Number of Beams	2 - Horizontal, Vertical
Tripod Connection	1/4"
Laser Class	2
Modes	Vertical Only, Horizontal Only, Cross Line
Power Source	2 x AAA



ALSO AVAILABLE AS:

DW088KD (INCLUDES DETECTOR)



CROSS LINE LASER (GREEN BEAM)

DW088CG

Beam Colour	Green
Accuracy	+/-3 mm @ 10m
Self-Levelling Range	+/-4°
Max. Working Range with Detector	20-50m
IP Rating	54
Number of Beams	3 - Horizontal, Vertical, Side
Tripod Connection	5/8"
Laser Class	2
Modes	3 beams Separately 1 Horizontal, 2 Vertical
Power Source	4 x AA



ALSO AVAILABLE AS:

DW088CGD (INCLUDES DETECTOR)

