

PILOT POINT® GOLD FERROUS OXIDE DRILL BITS

- PILOT POINT® tip starts on contact, drills clean, accurate holes and reduces burrs that cause lock-up on breakthrough
- Tapered web provides greater durability to reduce breakage
- Size markings located above the shank to prevent wearing away
- No-spin shank eliminates #1 user complaint – bit spinning in the chuck



Cat #	Qty/Card	Bulk Cat#	Bulk Qty	Dia Inches	Dia Decimal	Drilling Depth	Overall Length
DW1904	2	DW1904B	12	1/16"	.0625	.88	1.88
DW1905	2	DW1905B	12	5/64"	.0781	1.00	2.00
DW1906	2	DW1906B	12	3/32"	.0938	1.25	2.25
DW1907	2	DW1907B	12	7/64"	.1094	1.50	2.62
DW1908	2	DW1908B	12	1/8"	.1250	1.62	2.75
DW1909	1	DW1909B	12	9/64"	.1406	1.75	2.88
DW1910	1	DW1910B	12	5/32"	.1562	2.00	3.12
DW1911	1	DW1911B	12	11/64"	.1719	2.12	3.25
DW1912	1	DW1912B	12	3/16"	.1875	2.31	3.50
DW1913	1	DW1913B	12	13/64"	.2031	2.44	3.62
DW1914	1	DW1914B	12	7/32"	.2188	2.50	3.75
DW1915	1	DW1915B	12	15/64"	.2344	2.62	3.88
DW1916	1	DW1916B	12	1/4"	.2500	2.75	4.00
DW1917	1	DW1917B	12	17/64"	.2656	2.88	4.12
DW1918	1	DW1918B	12	9/32"	.2812	2.94	4.25
DW1919	1	DW1919B	12	19/64"	.2969	3.06	4.38
DW1920	1	DW1920B	6	5/16"	.3125	3.19	4.50
DW1921	1	DW1921B	6	21/64"	.3281	3.31	4.62
DW1922	1	DW1922B	6	11/32"	.3438	3.44	4.75
DW1923	1	DW1923B	6	23/64"	.3594	3.50	4.88
DW1924	1	DW1924B	6	3/8"	.3750	3.62	5.00
DW1925*	1	DW1925B*	6	25/64"	.3906	3.75	5.12
DW1926*	1	DW1926B*	6	13/32"	.4062	3.88	5.25
DW1927*	1	DW1927B*	6	27/64"	.4219	3.94	5.38
DW1928*	1	DW1928B*	6	7/16"	.4375	4.06	5.50
DW1929*	1	DW1929B*	6	29/64"	.4531	4.19	5.62
DW1930*	1	DW1930B*	6	15/32"	.4688	4.31	5.75
DW1931*	1	DW1931B*	6	31/64"	.4844	4.38	5.88
DW1932*	1	DW1932B*	6	1/2"	.5000	4.50	6.00

Sets Description

DW1169 14-Pc. Set with TOUGH CASE™ container Contains: (2) 1/16", 5/64", 3/32", 7/64", (2) 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16", 3/8"

DW1956 16-Pc. Set with TOUGH CASE™ container Contains: (2) 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 11/64", 3/16", 13/64", 7/32", 1/4", 5/16", 3/8", 1/2"

DW1969 29-Pc. Set with TOUGH CASE™ container Contains: 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 11/64", 3/16", 13/64", 7/32", 15/64", 1/4", 17/64", 9/32", 19/64", 5/16", 21/64", 11/32", 23/64", 3/8", 25/64", 13/32", 27/64", 7/16", 29/64", 15/32", 31/64", 1/2"

*3/8" reduced shank



TOUGH CASE™ DRILLING CASES

- Industrial grade ABS material for maximum durability
- Interlocking hinge for longer life
- Sliding rubber lock keeps case closed
- Bit holder system keeps bits in place and identifies sizes

