



**DW090PK  
20x Builders Level Package**

- 20x magnification for 200'+ range
- $\pm 1/4$ " per 100' accuracy
- 360° horizontal circle with vernier scale for precise measuring of horizontal angles
- Heavy-duty leveling base is fast & easy to setup and level
- Protected leveling vial for jobsite durability

**INCLUDES:** heavy-duty aluminum tripod w/quick adjust legs and heavy-duty 8' aluminum grade rod (feet-inches-eighths)



**DW092PK  
20x Transit Level Package**

- 20x magnification for 200'+ range
- $\pm 1/4$ " per 100' accuracy
- Transit capability allows user to determine vertical angles
- 360° horizontal circle with vernier scale for precise measuring of horizontal angles
- Protected leveling vial for jobsite durability
- Heavy-duty leveling base is fast & easy to setup and level

**INCLUDES:** heavy-duty aluminum tripod w/quick adjust legs and heavy-duty 8' aluminum grade rod (feet-inches-eighths)



**DW096PK  
26x Auto Level Package**

- Magnetically dampened compensator for easy setup with optimum range and accuracy
- 26x magnification for 300'+ range
- $\pm 1/32$ " per 100' accuracy
- Heavy-duty leveling base is fast & easy to setup and level
- 360° horizontal circle for precise measuring of horizontal angles

**INCLUDES:** heavy-duty aluminum tripod w/quick adjust legs and heavy-duty 8' aluminum grade rod (feet-inches-eighths)

<b>SPECIFICATIONS</b>	<b>DW090PK</b>	<b>DW092PK</b>	<b>DW096PK</b>
Leveling Type	Manual	Manual	Auto
Accuracy @ 100 ft.	$\pm 1/4$ in	$\pm 1/4$ in	$\pm 1/32$ in
Magnification	20x	20x	26x
Range	200 ft	200 ft	300 ft
Stadia Ratio	1:100	1:100	1:100
Horizontal Circle Type	Continuous Drive	Continuous Drive	Continuous Drive