

IMPACT WRENCHES



1/2" Impact Wrench

1/2" Impact Wrench

3/4" Impact Wrench

3/4" Impact Wrench

SPECIFICATIONS	DW292/K	DW293	DW294	DW297
Amps	7.5 Amps	7.5 Amps	7.5 Amps	7.5 Amps
No Load Speed	2,100 rpm	2,100 rpm	2,100 rpm	1,600 rpm
Max. Torque	345 ft-lbs	345 ft-lbs	345 ft-lbs	434 ft-lbs
Impacts/Min	2,700 ipm	2,700 ipm	2,700 ipm	1,800 ipm
Anvil Type	Detent Pin	Hog Ring	Detent Pin	Detent Pin
Tool Length	11-1/4"	11-1/4"	11-1/4"	13"
Tool Weight	7.0 lbs	7.0 lbs	7.0 lbs	11.0 lbs

CUT-OUT TOOL



Cut-Out Tool

SPECIFICATIONS	DW660
Amps	5.0 Amps
No Load Speed	30,000 rpm
Collet Diameter	1/8", 1/4"
Adjustable Guide	Yes
Spindle Lock	Yes
Tool Length	10"
Tool Weight	3.2 lbs

3/8" VSR DRILLS



3/8" VSR Mid-Handle Drill Kit with Keyless Chuck

3/8" VSR Pistol Grip Drill with Keyless Chuck

3/8" VSR Pistol Grip Drill Kit with Keyless Chuck

3/8" VSR Drill

3/8" VSR Drill

3/8" VSR Drill with Keyless Chuck

SPECIFICATIONS	DWD115K	DWD112	DWD110K	D21002	DW223G	DW222
Chuck Size	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Keyless Chuck	Yes	Yes	Yes	N/A	No	Yes
Amps	8.0 Amps	8.0 Amps	8.0 Amps	6.0 Amps	7.0 Amps	6.7 Amps
No Load Speed	0-2,500 rpm	0-2,500 rpm	0-2,500 rpm	0-2,500 rpm	0-1,200 rpm	0-1,200 rpm
Max Watts Out	650 W	650 W	650 W	480 W	560 W	520 W
Capacity In Wood (Spade Bit)	1"	1"	1"	1"	1-1/4"	1-1/4"
Capacity In Wood (Hole Saw)	1-1/8"	1-1/8"	1-1/8"	1-1/8"	2-1/8"	2-1/8"
Capacity In Steel (Twist Bit)	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Tool Weight	4.1 lbs	4.1 lbs	4.1 lbs	3.2 lbs	3.6 lbs	3.3 lbs

DWD115K



VSR DRILLS



1/4" VSR Drill



3/8" VSR Right Angle Drill

SPECIFICATIONS	DW217	DW160V
Chuck Size	1/4"	3/8"
Amps	6.7 Amps	4.0 Amps
No Load Speed	0-4,000 rpm	0-1,200 rpm
Max Watts Out	510 W	200 W
Keyless Chuck	No	No
Capacity In Wood (Spade Bit)	3/4"	1-1/8"
Capacity In Wood (Hole Saw)	N/A	1-1/8"
Capacity In Steel (Twist Bit)	1/4"	3/8"
Tool Weight	3.2 lbs	3.75 lbs