



HEAVY DUTY WALKIE-TALKIE

Up to 300,000 sq.ft./25 Floors

Provides extended signal range with 2662 channel combinations.

22 Preset Channels

Channels are preset with Privacy codes to minimize unwanted interference from others.

IP67 Rating

Dust Resistant & Waterproof

Shock Resistant

Can withstand 2M drop

180° Swivel Holster

Allows to rotate sideways for multiple positions.

VOX

Voice-activated transmission frees hands for other tasks.

Vibration Alert

Enhanced vibrating feedback to notify you of incoming transmissions.

DXFRS800



GUARANTEED TOUGH.®

www.DeWalt.com

DXFRS800

Features

Benefits

UHF/FM	Ultra-clear long distance reception.
300,000 sq.ft./25 Floors Range	Up to 300,000 sq.ft./25 floor range.(Range will vary depending on terrain and conditions.)
22 Preset Channels	22 channels have been preset with privacy codes to minimize unwanted interference from others.
121 Privacy Codes	38 CTCSS (Continuous Tone Coded Squelch System) codes and 83 DCS (Digitally Coded Squelch) codes provide a total of 121 privacy codes. 2662 privacy combinations are possible when the 22 channels are combined with the 121 privacy codes.
VOX (Voice Activated Transmission)	User's voice is detected and the radio transmits without the need to press any buttons, freeing the user's hands for other tasks. 5 VOX sensitivity levels allow user to select at which point the radio will detect their voice.
Roger Beep Tone	Confirmation tone indicates the completion of the user's transmission, and signals others it is clear to talk.
Key Lock	Provides key pad security eliminating accidental channel changes when activated.
Power Saver	A unique circuit extends the life of your batteries. If there are no transmissions within 10 seconds, the unit will automatically switch to battery save mode.
Auto Squelch	Automatically shuts off weak transmissions or unwanted noise due to terrain or range constraints.
Blue Backlit LCD Display	Easy to view display provides the radio's status at a glance.
Speaker/Microphone/Jack	Allows use of wall charger, or earphone speaker/microphones (not included) for "hands-free" operation.
180° Swivel Holster	Secures your radio while on the go.
No Licence or Service Fees	High quality band frequencies with no fees.
Volume Knob	Allow user to adjust any volume level easily and promptly.
Charging Dock	Reversible charging mechanism designed for most convenient drop-in charging.
IP67 Rating	Dust Resistant & Waterproof
Shock Resistant	Can withstand 2M drop.
Limited Lifetime Warranty	Pledge to replace product that is defective in material or workmanship as long as you are the original purchaser.
Vibration Alert	Enhanced vibrating feedback to notify you of incoming transmissions.
Anti-Slip Design	For more assured handling, helps prevent from dropping the radio.
Ultra Long Runtime	Can continue to use 18 hours (90% Standby / 5% Talk / 5% Listen).
USB-C charging	Convenient for charging.

Unit Specifications - General *Specifications subject to change without notice*

All dimensions (H x W x D)

22 Channels with Default Privacy Code						SKU#	DXFRS800	Package Contents	Radios x 2 2000mAh Rechargeable Lithium Polymer Batteries x 2 Dual port charging dock x 1	
UPC						8 5003551502 0	RF Output	2W	Master Package Dimension	9.65" x 15.16" x 13.19"
Radio Unit Dimension						7.25" x 2.38" x 1.35"	Radio Unit Weight	0.44 lbs w/ batteries	Master Pack Qty	4
Package Dimension						12.60" x 8.66" x 3.94"	Package Weight	1.82 lbs	Master Pack Weight	8.55 lbs

Channel	Privacy Code		Channel	Privacy Code	
	Type	Number		Type	Number
1	CTCSS	1	12	DCS	77
2	CTCSS	11	13	CTCSS	1
3	CTCSS	22	14	CTCSS	11
4	CTCSS	33	15	CTCSS	22
5	DCS	1	16	CTCSS	33
6	DCS	11	17	DCS	1
7	DCS	22	18	DCS	11
8	DCS	33	19	DCS	22
9	DCS	44	20	DCS	33
10	DCS	55	21	DCS	44
11	DCS	66	22	DCS	55

Copyright© 2023 DEWALT.
DEWALT® and the DEWALT Logo are trademarks of the DEWALT Industrial Tool Co., or an affiliate thereof and are used under license.
The yellow/black color scheme is a trademark for DEWALT power tools & accessories.

©2023 Shine Flex US LLC, Illinois, USA.

GUARANTEED TOUGH.®

DXFRS800 20230109