

Push-On Hose Barb Fittings

Application

- Intended for use with Lok-On (push-on style) hose only

Features

- No hose clamps or ferrules are needed for installation
- Properly grips push-on hose only when pushed all the way in, with the cut end of the hose completely concealed by the plastic cap



Female 45° SAE/37° JIC Swivel x Hose Barb

Hose I.D.	Tube O.D.	Female UNF	Brass			Lead-Free Brass ¹ Part #
			Previous Part #	Part #	Pkg Qty	
1/4"	1/4"	7/16"-20	287-0407	2870407C	100	2870407CLF
			---	2870407CBC ²	100	---
	5/16"	1/2"-20	287-0408	2870408C	100	---
			---	2870408CBC ²	100	---
3/8"	5/16"	1/2"-20	287-0608	2870608C	25	---
	1/2"	3/4"-16	287-0612	2870612C	25	---
1/2"	1/2"	3/4"-16	287-0812	2870812C	25	---
			---	2870812CBC ²	25	---
	5/8"	7/8"-14	287-0814	2870814C	25	---
			---	2870814CBC ²	25	---
5/8"	5/8"	7/8"-14	287-1014	2871014C	25	---
			---	2871014CBC ²	25	---
3/4"	5/8"	7/8"-14	287-1214	2871214C	25	---
			---	2871214CBC ²	25	---



plastic cap



brass cap



stainless steel

Hose I.D.	Tube O.D.	Female UNF	303 Stainless Steel	
			Previous Part #	Part #
1/4"	1/4"	7/16"-20	287-0407SS	2870407SS
1/2"	1/2"	3/4"-16	287-0812SS	2870812SS

¹ NSF®/ANSI 61 certified Lead-Free Brass <=0.25% lead, Alloy C2745

² Brass cap on CBC parts

Female 37° JIC Swivel x Hose Barb

Hose I.D.	Tube O.D.	Female UNF	Brass		Pkg Qty
			Previous Part #	Part #	
1/4"	3/8"	9/16"-18	288-0409	2880409C	50
			---	2880409CBC ¹	50
5/16"	3/8"	9/16"-18	288-0509	2880509C	50
3/8"	3/8"	9/16"-18	288-0609	2880609C	50
			---	2880609CBC ¹	100
1/2"	3/8"	9/16"-18	288-0809	2880809C	25
3/4"	3/4"	1-1/16"-12 ²	288-1217	2881217C	10
			---	2881217CBC ¹	10
1"	1"	1-5/16"-12 ²	288-1621	2881621C	10



brass



303 stainless steel

¹ Brass cap on CBC parts

Hose I.D.	Tube O.D.	Female UNF	303 Stainless Steel	
			Previous Part #	Part #
3/8"	3/8"	9/16"-18	288-0609SS	2880609SS
3/4"	3/4"	1-1/16"-12 ²	288-1217SS	2881217SS
1"	1"	1-5/16"-12 ²	288-1621SS	2881621SS

² UN Thread

Female 37° JIC / 45° SAE Swivel x 90° Elbow

Hose I.D.	Tube O.D.	Female UNF	Plated Steel		Pkg Qty
			Previous Part #	Part #	
1/4"	1/4"	7/16"-20	289-0407	2890407C ²	25
			289-0407SAE	2890407CSAE ¹	25
3/8"	3/8"	9/16"-18	289-0609	2890609C ²	25
		5/8"-18	289-0610SAE	2890610CSAE ¹	25
1/2"	1/2"	3/4"-16	289-0812	2890812C ²	10
3/4"	3/4"	1-1/16"-12 ³	289-1217	2891217C ²	5



¹ Notch in nut for SAE identification

² JIC only, may substitute dual angle

³ UN thread