



ASSORTMENT KITS — THREAD INSERTS FOR METAL

PREPACKAGED KITS CONTAINING A RANGE OF SIZES; DRILLS AND TAPS NOT INCLUDED

CARBON STEEL THREAD INSERTS FOR METAL — INCH/FINE THREAD

| Kit Type | Kit Number | Quantity of Inserts | Insert Part Number | Internal Thread | External Thread | Kit Type | Kit Number | Quantity of Inserts | Insert Part Number | Internal Thread | External Thread |
|--------------------------|------------|---------------------|--------------------|-----------------|-----------------|-------------------------|------------|---------------------|--------------------|-----------------|-----------------|
| Fine Thread #10 to 7/16" | EZ F107 | 10 | 329-332 | 10-32 | 3/8-16 | Fine Thread #10 to 1/2" | EZ F108T | 10 | 319-332 | 10-32 | 5/16-18 |
| | | 10 | 329-428 | 1/4-28 | 7/16-14 | | | 10 | 319-428 | 1/4-28 | 3/8-16 |
| | | 10 | 329-524 | 5/16-24 | 1/2-13 | | | 10 | 319-524 | 5/16-24 | 7/16-14 |
| | | 10 | 329-624 | 3/8-24 | 9/16-12 | | | 10 | 319-624 | 3/8-24 | 1/2-13 |
| | | 8 | 329-720 | 7/16-20 | 5/8-11 | | | 6 | 319-820 | 1/2-20 | 5/8-11 |
| Fine Thread #10 to 1/2" | EZ F108 | 10 | 329-332 | 10-32 | 3/8-16 | Fine Thread 1/2" to 1" | EZ F816 | 6 | 329-820 | 1/2-20 | 3/4-10 |
| | | 10 | 329-428 | 1/4-28 | 7/16-14 | | | 7 | 329-10F | 5/8-18 | 7/8-9 |
| | | 10 | 329-524 | 5/16-24 | 1/2-13 | | | 7 | 329-1216 | 3/4-16 | 1-8 |
| | | 10 | 329-624 | 3/8-24 | 9/16-12 | | | 2 | 329-1614 | 1-14 | 1-3/8-12 |
| | | 6 | 329-820 | 1/2-20 | 3/4-10 | | | | | | |

CARBON STEEL THREAD INSERTS FOR METAL — METRIC

| Kit Type | Kit Number | Quantity of Inserts | Insert Part Number | Internal Thread | External Thread | Kit Type | Kit Number | Quantity of Inserts | Insert Part Number | Internal Thread | External Thread |
|-------------------------|------------|---------------------|--------------------|-----------------|-----------------|---------------------------|------------|---------------------|--------------------|-----------------|-----------------|
| Metric Thread M3 to M8 | EZ M100 | 10 | 450-3 | M3-0.5 | M6-1.0 | Metric Thread #10 to 1/2" | EZ M508 | 10 | 550-1024 | 10-32 | M8-1.25 |
| | | 10 | 450-4 | M4-0.7 | M8-1.25 | | | 10 | 550-1420 | 1/4-28 | M10-1.5 |
| | | 10 | 450-5 | M5-0.8 | M8-1.25 | | | 10 | 550-5 | 5/16-24 | M12-1.75 |
| | | 10 | 450-6 | M6-1.0 | M10-1.5 | | | 8 | 550-6 | 3/8-24 | M16-2.0 |
| | | 10 | 450-8 | M8-1.25 | M12-1.75 | | | 6 | 550-8 | 1/2-20 | M16-2.0 |
| Metric Thread M8 to M16 | EZ M200 | 10 | 450-8 | M8-1.25 | M12-1.75 | Metric Thread M6 to M12 | EZ M612 | 10 | 650-6 | M6-1.0 | 3/8-16 |
| | | 10 | 450-10 | M10-1.5 | M16-2.0 | | | 10 | 650-8 | M8-1.25 | 1/2-13 |
| | | 8 | 450-12 | M12-1.75 | M16-2.0 | | | 10 | 650-10 | M10-1.5 | 9/16-12 |
| | | 5 | 450-16 | M16-2.0 | M24-3.0 | | | 6 | 650-12 | M12-1.75 | 3/4-10 |

STAINLESS STEEL THREAD INSERTS FOR METAL

| Kit Type | Kit Number | Quantity of Inserts | Insert Part Number | Internal Thread | External Thread | Kit Type | Kit Number | Quantity of Inserts | Insert Part Number | Internal Thread | External Thread |
|---|------------|---------------------|--------------------|-----------------|-----------------|---------------------------------------|------------|---------------------|--------------------|-----------------|-----------------|
| Coarse Thread 303 Stainless #10 to 1/2" | EZ C303 | 10 | 303-3 | 10-24 | 3/8-16 | Metric Thread 303 Stainless M3 to M8 | EZ M103 | 10 | 453-3 | M3-0.5 | M6-1.0 |
| | | 10 | 303-4 | 1/4-20 | 7/16-14 | | | 10 | 453-4 | M4-0.7 | M8-1.25 |
| | | 10 | 303-5 | 5/16-18 | 1/2-13 | | | 10 | 453-5 | M5-0.8 | M8-1.25 |
| | | 10 | 303-6 | 3/8-16 | 9/16-12 | | | 10 | 453-6 | M6-1.0 | M10-1.5 |
| | | 6 | 303-8 | 1/2-13 | 3/4-10 | | | 10 | 453-8 | M8-1.25 | M12-1.75 |
| Coarse Thread Thin Wall 313 Stainless #10 to 1/2" | EZ C313 | 10 | 313-3 | 10-24 | 5/16-24 | Metric Thread 303 Stainless M8 to M16 | EZ M203 | 10 | 453-8 | M8-1.25 | M12-1.75 |
| | | 10 | 313-4 | 1/4-20 | 3/8-24 | | | 10 | 453-10 | M10-1.5 | M16-2.0 |
| | | 10 | 313-5 | 5/16-18 | 7/16-20 | | | 8 | 453-12 | M12-1.75 | M16-2.0 |
| | | 10 | 313-6 | 3/8-16 | 1/2-20 | | | 5 | 453-16 | M16-2.0 | M24-3.0 |
| | | 8 | 313-8 | 1/2-13 | 5/8-18 | | | 10 | 653-6 | M6-1.0 | 3/8-16 |
| Fine Thread 303 Stainless #10 to 1/2" | EZ F303 | 10 | 303-332 | 10-32 | 3/8-16 | Metric Thread 303 Stainless M6 to M12 | EZ M613 | 10 | 653-8 | M8-1.25 | 1/2-13 |
| | | 10 | 303-428 | 1/4-28 | 7/16-14 | | | 10 | 653-10 | M10-1.5 | 9/16-12 |
| | | 10 | 303-524 | 5/16-24 | 1/2-13 | | | 6 | 653-12 | M12-1.75 | 3/4-10 |
| | | 10 | 303-624 | 3/8-24 | 9/16-12 | | | | | | |
| Fine Thread Thin Wall 313 Stainless #10 to 1/2" | EZ F313 | 10 | 313-332 | 10-32 | 5/16-24 | | | | | | |
| | | 10 | 313-428 | 1/4-28 | 3/8-24 | | | | | | |
| | | 10 | 313-524 | 5/16-24 | 7/16-20 | | | | | | |
| | | 10 | 313-624 | 3/8-24 | 1/2-20 | | | | | | |
| | | 8 | 313-820 | 1/2-20 | 5/8-18 | | | | | | |

