



Powering Business Worldwide

pe.eaton.com

HLE Helix Type Current Limiting Fuse

15HLE-10E-Q

UPC:786670008125

Dimensions:

- **Height:** 6 IN
- **Length:** 18.87 IN
- **Width:** 19 IN

Weight:9 LB

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** HLE
- **Application:** Indoor / Outdoor
- **Amperage Rating:** 10A
- **Barrels:** Single barrel
- **Diameter:** 3 IN
- **Interrupt Rating:** 63 kAIC
- **Class:** E
- **Maximum Voltage:** 15.5 kV
- **Nominal Voltage:** 14.4 kV

Supporting documents:

- [Eaton Specification Sheet - 15HLE-10E-Q](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data



