



Powering Business Worldwide

pe.eaton.com

Midsize AC rated High Inrush Non-illuminated Rocker

1600HMA21E

UPC:782116548675

Dimensions:

- **Height:** .982 IN
- **Length:** 1.197 IN
- **Width:** X

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 22A at 125 Vac, 16A at 250 Vac, 6A at 125 Vac, 10A at 14VT, ENEC: 16(4)A at 250V
- **Circuit Number:** 1
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** ON
- **Frame Color:** Black
- **Horsepower:** 1 hp at 125-250 Vac
- **Illumination:** Non-illuminated
- **Lamp Voltage:** 250V
- **Number Of Poles:** Single-pole
- **Rocker Color:** Amber
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Single-throw

Supporting documents:

- [Eaton Specification Sheet - 1600HMA21E](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.