



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Midsize AC Rated Illuminated Rocker

**1600MG51E122BO**

**UPC:**782116548828

### Dimensions:

- **Height:** .982 IN
- **Length:** 1.197 IN
- **Width:** X

**Notes:**Graphic can be found on Page V11-T2-53. 3-digit code specifies

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

### Specifications:

- **Amperage Rating:** 16A at 125-250 Vac, 10A at 28 Vdc, 8A at 14VT, ENEC: 16(4)A at 250V
- **Circuit Number:** 1
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** ON
- **Frame Color:** Black
- **Illumination:** Illuminated
- **Lamp Voltage:** 12V filament
- **Number Of Poles:** Single-pole
- **Rocker Color:** Green
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Single-throw

### Supporting documents:

- [Eaton Specification Sheet - 1600MG51E122BO](#)

**Certifications:** No Data



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.